

Content

1	Firmware Release 04.04.03 (26) – CODESYS 3.....	2
2	Firmware Release 04.03.03 (25) – CODESYS 3.....	5
3	Firmware Release 04.02.13 (24) – CODESYS 3.....	8
4	Firmware Release 04.01.10 (23) – CODESYS 3.....	12
5	Firmware Release 03.10.10 (22) – e!COCKPIT and CODESYS 2.....	15
6	Firmware Release 03.10.08 (22) – e!COCKPIT and CODESYS 2.....	18
7	Firmware Release 03.09.05 (21) – e!COCKPIT and CODESYS 2.....	22
8	Firmware Release 03.09.04 (21) – e!COCKPIT and CODESYS 2.....	23
9	Firmware Release 03.08.08 (20).....	26
10	Firmware Release 03.08.07 (20).....	26
11	Firmware Release 03.07.14 (19).....	30
12	Firmware Release 03.06.19 (18).....	34
13	Firmware Release 03.06.11 (18).....	35
14	Firmware Release 03.06.09 (18).....	36
15	Firmware Release 03.05.10 (17).....	39
16	Firmware Release 03.04.10 (16).....	42
17	Firmware Release 03.03.11 (15).....	44
18	Firmware Release 03.03.10 (15).....	45
19	Firmware Release 03.02.02 (14).....	47
20	Firmware Release 03.01.07 (13).....	49
21	Firmware Release 03.00.39 (12).....	50
22	Firmware Release 03.00.35 (12).....	52
23	Firmware Release 02.08.35 (11).....	54
24	Firmware Release 02.08.31 (11).....	54
25	Firmware Release 02.08.26 (11).....	55
26	Firmware Release 02.08.25 (11).....	55
27	Firmware Release 02.07.07 (10).....	57
28	Firmware Release 02.06.20 (09).....	59
29	Firmware Release 02.05.23 (08).....	62
30	Firmware Release 02.04.24 (07).....	63
31	Firmware Release 02.04.22 (06).....	64
32	Firmware Release 02.04.21 (05).....	68
33	Firmware Release 02.02.20 (03).....	71
34	Firmware Release 02.01.10 (02).....	73
35	Firmware Release 02.01.04 (01).....	74

Engineering with CODESYS 3 then use Firmware 04.xx.xx
 Engineering with CODESYS 2 then use Firmware 03.xx.xx
 Engineering with e!COCKPIT then use Firmware 03.xx.xx

1 Firmware Release 04.04.03 (26) – CODESYS 3

Engineering by CODESYS IDE V. 3.5 is supported

Engineering by e!COCKPIT IDE is not supported

CODESYS 2.3 is not supported

Migration Guide – from e!COCKPIT to CODESYS V3.5:

- https://techdocs.wago.com/Software/eCOCKPIT_Migration/en-US/index.html#index_content

BUG FIX

SECURITY RELEVANT

NEW FEATURES

Tested and released with:	
CODESYS 64 Bit version	3.5.19.2
Device description CODESYS	2.0.4.2

Affected articles/Available for		Supported PLC CODESYS Runtime
Article Number	Designation	
750-8210	PFC200 G2 4ETH	X
750-8210/025-000	PFC200 G2 4ETH T	X
750-8210/040-000	PFC200 G2 4ETH XTR	X
750-8211	PFC200 G2 2ETH 2SFP	X
750-8211/040-000	PFC200 G2 2ETH 2SFP T	X
750-8211/040-001	PFC200 G2 2ETH 2SFP Tele T	X
750-8212	PFC200 G2 2ETH RS	X
750-8212/000-100	PFC200 G2 2ETH RS BACnet/IP	X
750-8212/025-000	PFC200 G2 2ETH RS T	X
750-8212/025-001	PFC200 G2 2ETH RS Tele T	X
750-8212/025-002	PFC200 G2 2ETH RS ECO Tele T	X
750-8212/040-000	PFC200 G2 2ETH RS XTR	X
750-8212/040-001	PFC200 G2 2ETH RS Tele XTR	X
750-8212/040-010	PFC200 G2 2ETH M12 RS XTR	X
750-8213	PFC200 G2 2ETH CAN	X
750-8213/040-010	PFC200 G2 2ETH M12 CAN XTR	X
750-8214	PFC200 G2 2ETH RS CAN	X
750-8215	PFC200 G2 4ETH CAN USB	X
750-8216	PFC200 G2 2ETH RS CAN DPS	X
750-8216/025-000	PFC200 G2 2ETH RS CAN DPS T	X
750-8216/025-001	PFC200 G2 2ETH RS CAN DPS Tele T	X
750-8216/040-000	PFC200 G2 2ETH RS CAN DPS XTR	X
750-8217	PFC200 G2 2ETH RS 4G EU	X
750-8217/025-000	PFC200 G2 2ETH RS 4G EU T	X
750-8217/600-000	PFC200 G2 2ETH RS 4G Global	X
750-8217/625-000	PFC200 G2 2ETH RS 4G Global T	X

This firmware will be released via GitHub: <https://github.com/WAGO>

1.1 System

- [FIXED] WAT-35959 Sporadic failure of data communication to the cloud
- [FIXED] WAT-35833 NTP client timeout too short. Increased to 8 sec.
- [FIXED] WAT-35777 If the device is in separate mode and no web server is running, the fire wall blocks the webserver after armed, regardless of how the firewall is set
- [FIXED] WAT-35759 APN configuration leads to modem reset

[FIXED]	WAT-35816	FTP didn't support NOOP command
[FIXED]	WAT-35837	Ensure UTF-8 encoding for log files
[DEPRECATED]		The network feature rate limiting is deprecated and will be removed in future versions
[Note]	ADVICE	Code generation from WDA OpenAPI is possible via Postman

1.2 Operating System

[FIXED]	SECURITY	CVE-2023-27533, CVE-2023-27534, CVE-2023-27535, CVE-2023-27536, CVE-2023-27537, CVE-2023-27538,
[CHANGED]		Update rauc to v1.9

1.3 Runtime System

[NEW]		CODESYS3 Runtime-System 3.5.19.20
[NEW]		CODESYS Redundancy. Needs DRM license 2759-249/210-1000 or 2759-249/211-1000
[FIXED]	WAT-35499	Data Sources Manager didn't support Application V3
[CHANGED]		Access blocking for 1h after 5 login failures
[CHANGED]	WAT-36061	Runtime file access is limited to /home/codesys, /media/sd, /tmp
[CHANGED]		The restriction to WAGO Ethernet Sub Devices has been removed for compatibility reasons
[FIXED]	SECURITY	CVE-2022-4224, CVE-2022-47378, CVE-2022-47379, CVE-2022-47380, CVE-2022-47381, CVE-2022-47382, CVE-2022-47383, CVE-2022-47384, CVE-2022-47385, CVE-2022-47386, CVE-2022-47387, CVE-2022-47388, CVE-2022-47389, CVE-2022-47390, CVE-2022-47392, CVE-2022-47393, CVE-2022-47391, CVE-2023-37545, CVE-2023-37546, CVE-2023-37547, CVE-2023-37548, CVE-2023-37549, CVE-2023-37550, CVE-2023-37551, CVE-2023-37552, CVE-2023-37553, CVE-2023-37554, CVE-2023-37555, CVE-2023-37556, CVE-2023-37557, CVE-2023-37558, CVE-2023-37559, CODESYS IDE: CVE-2023-3662, CVE-2023-3663, CVE-2023-3669,

1.4 Fieldbus Interface & Protocols

[NEW]		Modbus RTU: CODESYS configurator for the onboard serial interface
[NEW]		PROFINET: Limited support of CODESYS PROFINET controller and device
[NOTE]	IMPORTANT	PROFINET: no MRP ring redundancy, no LLDP support, no Daisy Chain wiring, limited to one Ethernet port

[NOTE]	ADVICE	PROFINET: do not use the controller with more than 5 devices
[FIXED]	WAT-36007	BACnet: Max/Min Pres Value Property in Analog Input Objects
[FIXED]	WAT-35967	BACnet: Sporadic missing synchronicity between runtime and BACnet objects
[FIXED]	WAT-35896	BACnet: Synchronization if an override configuration file exists with objects that have more properties defined in the configuration file than in CODESYS
[FIXED]	WAT-35861	BACnet: Non alphanumeric characters in Trendlog object name
[FIXED]	WAT-35428	OPC UA Client: CmpOPCUAClient stops the runtime if the connected server is shut down.

1.5 Libraries

[NEW]	WAT-35633	WagoSysModem 2.0.1.0: Send SMS in text mode
[NEW]	WAT-35576	WagoSyCurl: Support for WSTRING
[NEW]	WAT-35445	WagoAppCloud: Support for data types SINT, LINT, ULINT and LWORD

1.6 Web Based Management

[FIXED]	WAT-35775	Automatically redirect to application didn't work if separate ports are enabled for WBM and WebVisu.
[FIXED]	SECURITY	CVE-2023-3379, CVE-2023-3378
[CHANGED]	SECURITY	Page SNMP v3 the keys are now only displayed masked

The Release Note(s) and the corresponding update(s) are provided free of charge. The statutory warranty and liability regulations of §§ 521, 523 BGB apply to possible errors in the Release Note(s) or possible defects in the update (CISG is excluded). The update(s) is (are) intended to further enhance and / or to enrich our product(s), but does not mean that the previous software version was defective. In order to benefit from the improvements, we generally recommend the implementation of the update(s), but we cannot assume the final responsibility for the installation of the update(s) or their costs. Since we know neither the concrete application nor the individual conditions of use.

2 Firmware Release 04.03.03 (25) – CODESYS 3

Engineering by CODESYS IDE V. 3.5 is supported

Engineering by e!COCKPIT IDE is not supported

CODESYS 2.3 is not supported

Migration Guide – from e!COCKPIT to CODESYS V3.5:

- https://techdocs.wago.com/Software/eCOCKPIT_Migration/en-US/index.html#index_content

BUG FIX

SECURITY RELEVANT

NEW FEATURES

Tested and released with:	
CODESYS 64 Bit version	3.5.18.4 / 3.5.18.5
Device Description CODESYS	2.0.2.9

Affected articles/Available for		Supported PLC CODESYS Runtime
Article Number	Designation	
750-8210	PFC200 G2 4ETH	X
750-8210/025-000	PFC200 G2 4ETH T	X
750-8210/040-000	PFC200 G2 4ETH XTR	X
750-8211	PFC200 G2 2ETH 2SFP	X
750-8211/040-000	PFC200 G2 2ETH 2SFP T	X
750-8211/040-001	PFC200 G2 2ETH 2SFP Tele T	X
750-8212	PFC200 G2 2ETH RS	X
750-8212/000-100	PFC200 G2 2ETH RS BACnet/IP	X
750-8212/025-000	PFC200 G2 2ETH RS T	X
750-8212/025-001	PFC200 G2 2ETH RS Tele T	X
750-8212/025-002	PFC200 G2 2ETH RS ECO Tele T	X
750-8212/040-000	PFC200 G2 2ETH RS XTR	X
750-8212/040-001	PFC200 G2 2ETH RS Tele XTR	X
750-8212/040-010	PFC200 G2 2ETH M12 RS XTR	X
750-8213	PFC200 G2 2ETH CAN	X
750-8213/040-010	PFC200 G2 2ETH M12 CAN XTR	X
750-8214	PFC200 G2 2ETH RS CAN	X
750-8215	PFC200 G2 4ETH CAN USB	X
750-8216	PFC200 G2 2ETH RS CAN DPS	X
750-8216/025-000	PFC200 G2 2ETH RS CAN DPS T	X
750-8216/025-001	PFC200 G2 2ETH RS CAN DPS Tele T	X
750-8216/040-000	PFC200 G2 2ETH RS CAN DPS XTR	X
750-8217	PFC200 G2 2ETH RS 4G EU	X
750-8217/025-000	PFC200 G2 2ETH RS 4G EU T	X
750-8217/600-000	PFC200 G2 2ETH RS 4G Global	X
750-8217/625-000	PFC200 G2 2ETH RS 4G Global T	X

This firmware will be released via GitHub: <https://github.com/WAGO>

2.1 System

[NEW]		Support for Azure IoT Hub Device Provisioning Service (DSP)
[NEW]		VLAN and Dummy interfaces can be configured via WAGO Device Manager (WDM)
[FIXED]	WAT-35470	Does not try to connect to all configured NTP servers after a connection failure with the original server
[FIXED]	WAT-35369	Sometimes it does not load all firewall rules and block legitimate traffic

[KNOWN]	WAT-35777	If separated ports are setup for WebVisu and WBM and no CODESYS webserver is running, the WebVisu port will be blocked by the firewall as soon as the firewall is armed, regardless of the setting of the firewall. Workaround: 1) temporarily disable the firewall, 2) switch on CODESYS web server, 3) switch on the firewall again
[REMOVED]		DNS-server and DHCP-server (dnsmasq) are removed
[CHANGED]		The library for the device abstraction layer (DAL) will be changed from a static (libdal.a) to a dynamic library (libdal.so). Libdal.a is deprecated and will be removed in future versions. Users should link against libdal.so
[RELEASED]		"Wago Device Access" for parametrization and configuration. REST-API is active under path "<host>/wda" on port 443. File-Access-API is active under path "<host>/files" on port 443. To disable the service, delete symlink "/etc/rc.d/S11_paramd" or move it to subdirectory "disabled"
[RELEASED]		A documentation for the REST-API of "Wago Device Access" is available from device by calling specified URL: OpenAPI-JSON: <ip/hostname>/openapi/wda.openapi.json HTML format: <ip/hostname>/openapi/wda.openapi.html

2.2 Operating System

[FIXED]	WAT-35575	Update curl to v8.0.1
[FIXED]	WAT-35630	Update OpenSSH to v9.3p1
[FIXED]	SECURITY	CVE-2023-23914, CVE-2023-23915, CVE-2023-23916, CVE-2023-28531

2.3 Runtime System

[NEW]		Codesys3 Runtime-System 3.5.18.40
[NEW]	WAT-35417	Add support for CODESYS 3 CoreDumps
[NEW]		Add support of PROFIBUS Device configuration for 750-8216
[FIXED]	SECURITY	CVE-2022-4048, CVE-2022-22515, CVE-2022-22508

2.4 Fieldbus Interface & Protocols

[FIXED]	WAT-35734	EtherNet/IP scanner 4.3.0.0 generates exception during simulation
[FIXED]	WAT-35600	SIGABRT exception on RESET COLD of MODBUS slave applications Workaround: Disable PLC Settings "always update variables"
[FIXED]	WAT-35635	WagoSysVisuBACnet library is supported with FW25

2.5 Libraries

- [NEW] Support of CODESYS IoT Libraries (Royalty free)
- [NEW] WagoSysModule_75x_511

2.6 Web Based Management

- Network configuration for vlan and dummy interfaces
- [NEW] New option on page "Port and Services – PLC Runtime Services" set a separate the interface for the PLC WebVisu
- [NEW] a separate the interface for the PLC WebVisu
- [FIXED] WAT-35423 The representation of UII number does not comply with the company standard
- [KNOWN] WAT-35775 With separate ports for the WebVisu and WBM there is no redirect to the set option WBM or WebVisu
Workaround: add "/wbm" or "/webvisu" to the URL

The Release Note(s) and the corresponding update(s) are provided free of charge. The statutory warranty and liability regulations of §§ 521, 523 BGB apply to possible errors in the Release Note(s) or possible defects in the update (CISG is excluded). The update(s) is (are) intended to further enhance and / or to enrich our product(s), but does not mean that the previous software version was defective. In order to benefit from the improvements, we generally recommend the implementation of the update(s), but we cannot assume the final responsibility for the installation of the update(s) or their costs. Since we know neither the concrete application nor the individual conditions of use.

3 Firmware Release 04.02.13 (24) – CODESYS 3

Engineering by CODESYS IDE V. 3.5 is supported
Engineering by e!COCKPIT IDE is not supported
CODESYS 2.3 is not supported

Migration Guide – from e!COCKPIT to CODESYS V3.5:

- https://techdocs.wago.com/Software/eCOCKPIT_Migration/en-US/index.html#index_content

BUG FIX

SECURITY RELEVANT

NEW FEATURES

Tested and released with:	
CODESYS 64 Bit version	3.5.18.2
Device Description CODESYS	2.0.1.7

Affected articles/Available for		Supported PLC CODESYS Runtime
Article Number	Designation	
750-8210	PFC200 G2 4ETH	X
750-8210/025-000	PFC200 G2 4ETH T	X
750-8210/040-000	PFC200 G2 4ETH XTR	X
750-8211	PFC200 G2 2ETH 2SFP	X
750-8211/040-000	PFC200 G2 2ETH 2SFP T	X
750-8211/040-001	PFC200 G2 2ETH 2SFP Tele T	X
750-8212	PFC200 G2 2ETH RS	X
750-8212/000-100	PFC200 G2 2ETH RS BACnet/IP	X
750-8212/025-000	PFC200 G2 2ETH RS T	X
750-8212/025-001	PFC200 G2 2ETH RS Tele T	X
750-8212/025-002	PFC200 G2 2ETH RS ECO Tele T	X
750-8212/040-000	PFC200 G2 2ETH RS XTR	X
750-8212/040-001	PFC200 G2 2ETH RS Tele XTR	X
750-8212/040-010	PFC200 G2 2ETH M12 RS XTR	X
750-8213	PFC200 G2 2ETH CAN	X
750-8213/040-010	PFC200 G2 2ETH M12 CAN XTR	X
750-8214	PFC200 G2 2ETH RS CAN	X
750-8215	PFC200 G2 4ETH CAN USB	X
750-8216	PFC200 G2 2ETH RS CAN DPS	X
750-8216/025-000	PFC200 G2 2ETH RS CAN DPS T	X
750-8216/025-001	PFC200 G2 2ETH RS CAN DPS Tele T	X
750-8216/040-000	PFC200 G2 2ETH RS CAN DPS XTR	X
750-8217	PFC200 G2 2ETH RS 4G EU	X
750-8217/025-000	PFC200 G2 2ETH RS 4G EU T	X
750-8217/600-000	PFC200 G2 2ETH RS 4G Global	X
750-8217/625-000	PFC200 G2 2ETH RS 4G Global T	X

This firmware will be released via GitHub: <https://github.com/WAGO>

3.1 System

[FIXED]	WAT33700	WAT-33700 Fixed erroneous logrotate configuration which leads to crash of CODESYS runtime when OpenVPN is used.
[DEPRECATED]		Config tool “config_mdmd” and “update_modem_firmware” will be removed in future firmware versions
[CHANGED]		Reduced CBM functionality to basic use cases

3.2 Operating System

- [FIXED] WAT-34644 Replaced Busybox wget by upstream wget
- [FIXED] SECURITY CVE-2022-0529, CVE-2022-0530, CVE-2022-35260, CVE-2022-32221, CVE-2013-4235, CVE-2022-43995, CVE-2022-44792, CVE-2022-44793, CVE-2022-43680, CVE-2022-2309, CVE-2022-40303, CVE-2022-40304, CVE-2022-40476, CVE-2022-2905, CVE-2022-35252, CVE-2022-40674, CVE-2022-40284, CVE-2022-1012, CVE-2022-37434, CVE-2021-33656, CVE-2022-2327, CVE-2022-36879, CVE-2022-1671, CVE-2022-34494, CVE-2022-34495, CVE-2020-35501, CVE-2022-1998, CVE-2022-30788, CVE-2022-30789, CVE-2022-30783, CVE-2022-30785, CVE-2022-30786, CVE-2022-30784, CVE-2022-1882, CVE-2022-32296, CVE-2022-29581, CVE-2022-30594, CVE-2022-1015, CVE-2022-1048, CVE-2022-1353, CVE-2022-29824, CVE-2022-29824, CVE-2022-1055, CVE-2022-28391, CVE-2022-37434, CVE-2021-45868, CVE-2022-27666, CVE-2022-23219, CVE-2022-23219, CVE-2022-1348, CVE-2022-23471, CVE-2022-31030, CVE-2022-45137, CVE-2022-45139, CVE-2022-45140
- [KNOWN] SECURITY Improper handling of unicode string could crash unzip 6.0(CVE-2021-4217)

3.3 Runtime System

- [NEW] Codesys3 Runtime-System 3.5.18.20
- [FIXED] WAT34984 Sporadic error while running the Codesys3 WebVisu with HTTP
- [FIXED] WAT-35177 "PLC load watchdog" might not work as expected: the plc load watchdog will detect (e.g. an endless loop) but the IEC task might not be stopped in any case. This might lead to a complete stop of the runtime process. As workaround and improve "hardening" of your IEC application we recommend to use an IEC Task watchdog on all your relevant IEC tasks in your IEC application.
- [FIXED] SECURITY CVE-2022-22516, CVE-2021-21863, CVE-2021-21864, CVE-2021-21865, CVE-2021-21866, CVE-2021-21867, CVE-2021-21868, CVE-2021-21869, CVE-2022-1794, CVE-2022-22517, CVE-2022-22518, CVE-2022-22513, CVE-2022-22514, CVE-2022-22519, CVE-2022-30791, CVE-2022-30792

3.4 Fieldbus Interface & Protocols

[NEW]		Support of CODESYS OPC UA Server and OPC UA Client
[NEW]		Support of CODESYS OPC UA PubSub Libraries
[KNOWN]	WAT-35428	If the subscription of the CmpOPCUAClient cannot be established correctly and the OPC UA server is then shut down, a SIGABRT occurs in Runtime.
	WAT-35373	
[KNOWN]		The "WagoSysVisuBACnet" library is not support with firmware 24
[CHANGED]		Saving trap receiver address after firmware up-/downgrade

3.5 Libraries

[NEW]		Support of CODESYS OPC UA PubSub Libraries (Royalty free)
[FIXED]	WAT-35113	Docker Bridge Networking not working with Docker Swarm
[REMOVED]		WagoAppEtherNetIP_Adapter and WagoSysEtherNetIP_Adapter Please use native CODESYS 3.5 EtherNet/IP adapter
[KNOWN]	WAT-34389	Simulation might fail with some libraries within IDE

3.6 Web Based Management

[NEW]		Update to PHP 8.1.9
[NEW]		Diagnostic information for Cloud-Connectivity on status page
[FIXED]	WAT-35149	Do not start a restore of the system package if the device has booted from the memory card
[FIXED]	WAT-34837	Leading digits for host names
[FIXED]	WAT-34741	Backup & Restore is executable by user "root"
[FIXED]	WAT-31492	Added note text to explain the hostname behavior
[REMOVED]		"guest" access
[CHANGED]		Description for the certificate folder and configuration

3.7 Beta functionalities

[BETA]		"Wago Device Access" for parametrization and configuration. REST-API is active under path "<host>/wda" on port 443. File-Access-API is active under path "<host>/files" on port 443. To disable the service, delete symlink "/etc/rc.d/S11_paramd" or move it to subdirectory "disabled"
[BETA]		A documentation for the REST-API of "Wago Device Access" is available from device by calling specified URL:

OpenAPI-JSON: <ip/hostname>/openapi/wda.openapi.json

HTML format: <ip/hostname>/openapi/wda.openapi.html

The Release Note(s) and the corresponding update(s) are provided free of charge. The statutory warranty and liability regulations of §§ 521, 523 BGB apply to possible errors in the Release Note(s) or possible defects in the update (CISG is excluded). The update(s) is (are) intended to further enhance and / or to enrich our product(s), but does not mean that the previous software version was defective. In order to benefit from the improvements, we generally recommend the implementation of the update(s), but we cannot assume the final responsibility for the installation of the update(s) or their costs. Since we know neither the concrete application nor the individual conditions of use.

4 Firmware Release 04.01.10 (23) – CODESYS 3

Engineering by CODESYS IDE V. 3.5 is supported

Engineering by e!COCKPIT IDE is not supported

CODESYS 2.3 will no longer be supported

Migration Guide – from e!COCKPIT to CODESYS V3.5:

- https://techdocs.wago.com/Software/eCOCKPIT_Migration/en-US/index.html#index_content

BUG FIX

SECURITY RELEVANT

NEW FEATURES

Tested and released with:	
CODESYS 64 Bit version	3.5.17.2
Device Description CODESYS	2.0.0.9

Affected articles/Available for		Supported PLC CODESYS Runtime
Article Number	Designation	
750-8210	PFC200 G2 4ETH	X
750-8210/025-000	PFC200 G2 4ETH T	X
750-8210/040-000	PFC200 G2 4ETH XTR	X
750-8211	PFC200 G2 2ETH 2SFP	X
750-8211/040-000	PFC200 G2 2ETH 2SFP T	X
750-8211/040-001	PFC200 G2 2ETH 2SFP Tele T	X
750-8212	PFC200 G2 2ETH RS	X
750-8212/000-100	PFC200 G2 2ETH RS BACnet/IP	X
750-8212/025-000	PFC200 G2 2ETH RS T	X
750-8212/025-001	PFC200 G2 2ETH RS Tele T	X
750-8212/025-002	PFC200 G2 2ETH RS ECO Tele T	X
750-8212/040-000	PFC200 G2 2ETH RS XTR	X
750-8212/040-001	PFC200 G2 2ETH RS Tele XTR	X
750-8212/040-010	PFC200 G2 2ETH M12 RS XTR	X
750-8213	PFC200 G2 2ETH CAN	X
750-8213/040-010	PFC200 G2 2ETH M12 CAN XTR	X
750-8214	PFC200 G2 2ETH RS CAN	X
750-8215	PFC200 G2 4ETH CAN USB	X
750-8216	PFC200 G2 2ETH RS CAN DPS	X
750-8216/025-000	PFC200 G2 2ETH RS CAN DPS T	X
750-8216/025-001	PFC200 G2 2ETH RS CAN DPS Tele T	X
750-8216/040-000	PFC200 G2 2ETH RS CAN DPS XTR	X
750-8217	PFC200 G2 2ETH RS 4G EU	
750-8217/025-000	PFC200 G2 2ETH RS 4G EU T	
750-8217/600-000	PFC200 G2 2ETH RS 4G Global	
750-8217/625-000	PFC200 G2 2ETH RS 4G Global T	

This firmware will be released via GitHub: <https://github.com/WAGO>

4.1 System

- [NEW] WAT-34301 The client ID for all running DHCP clients can be specified using the config tool network_config.
The assignment of the client ID via WBM/WDM is not supported.
- [FIXED] WAT-34828 It is possible to downgrade to a hardened FW-Image without network connection lost.

- [NEW] WAT-34811 Allow to access legacy serial number via config tool: get_coupler_details serial-number-legacy
- [DEPRECATED] PHP 7 will be replaced by PHP 8.

4.2 Operating System

- [FIXED] WAT-34301 Fixed erroneous logrotate configuration which leads to crash of CODESYS runtime when OpenVPN is used.
- [DEPRECATED] WAT-35120 The config tool "activate_download" is deprecated and will be removed in future versions.
- [FIXED] WAT-34783 MAC Address filter configuration is loaded at boot time not only in event of changed configuration.
- [FIXED] WAT-34796 MAC Address filter was active by default, from now on it is off as default (cf. IP firewall).
- [FIXED] WAT-34501 Fixed error that prevents restore of system backup when Docker is activated.

4.3 Runtime System

- [REMOVED] Codesys2 Runtime-System is no longer available on PFC Platform
- [CHANGED] Codesys3 Runtime-System supported on PFC Platform
- [KNOWN] WAT-35177 "PLC load watchdog" might not work as expected: the plc load watchdog will detect (e.g. an endless loop) but the IEC task might not be stopped in any case. This might lead to a complete stop of the runtime process. As workaround and improve "hardening" of your IEC application we recommend to use an IEC Task watchdog on all your relevant IEC tasks in your IEC application.

4.4 Fieldbus Interface & Protocols

- [REMOVED] The OPC UA Server and Client are not included in this Firmware.
-Will be available in an upcoming Firmware.
- [REMOVED] PROFINET and PROFIBUS are not included in this Firmware.
-Will be available in an upcoming Firmware.
- [CHANGED] MODBUS TCP changed to CODESYS solution
- [CHANGED] MODBUS RTU available only by IEC library

4.5 Libraries

- [KNOWN] WAT-34389 Simulation might fail with some libraries within IDE
- [KNOWN] WAT-34680 WagoAppEtherNetIP_Adapter: CommonPacketFormat Interfaces 4.2.0.0 causes compile errors. CommonPacketFormat Interfaces

3.5.17.0 must be used instead. In order to use the correct version CommonPacketFormat Interfaces 4.2.0.0 needs to be deinstalled via CODESYS library manager.

4.6 Web Based Management

- [NEW] SNMPv3: Add support for strong privacy and encryption.
Authentication: SHA224, SHA256, SHA384, SHA512
Encryption: AES128, AES192, AES192C, AES256, AES256C
- [CHANGED] Codesys 2 no longer available in "Information - PLC Runtime", "Configuration - PLC Runtime" and "Ports and Services - PLC Runtime Services". Removed WBM page "Fieldbus - Modbus" (WAGO Modbus implementation).
- [NEW] WBM - Firewall - MAC Address Filter Whitelist:
For the default entries, an additional description text is displayed to avoid incorrect operation.
- [FIXED] WAT-34837 Update WDX and Config Tools to allow leading digits for host names.

4.7 Beta functionalities

- [BETA] "Wago Device Access" for parametrization and configuration.
REST-API is active under path "<host>/wda" on port 443.
File-Access-API is active under path "<host>/files" on port 443.
To disable the service, delete symlink "/etc/rc.d/S11_paramd" or move it to subdirectory "disabled"
- [BETA] A documentation for the REST-API of "Wago Device Access" is available from device by calling specified URL:
OpenAPI-JSON: <ip/hostname>/openapi/wda.openapi.json
HTML format: <ip/hostname>/openapi/wda.openapi.html

The Release Note(s) and the corresponding update(s) are provided free of charge. The statutory warranty and liability regulations of §§ 521, 523 BGB apply to possible errors in the Release Note(s) or possible defects in the update (CISG is excluded). The update(s) is (are) intended to further enhance and / or to enrich our product(s), but does not mean that the previous software version was defective. In order to benefit from the improvements, we generally recommend the implementation of the update(s), but we cannot assume the final responsibility for the installation of the update(s) or their costs. Since we know neither the concrete application nor the individual conditions of use.

5 Firmware Release 03.10.10 (22) – e!COCKPIT and CODESYS 2

BUG FIX

SECURITY RELEVANT

Compatible from e!COCKPIT Version	1.11	Compatible from WAGO I/O PRO Version	2.3.9.61
-----------------------------------	------	--------------------------------------	----------

Affected articles/Available for		Supported PLC	
Article Number	Designation	CDS2.3	e!Runtime
750-8210	PFC200 G2 4ETH	X	X
750-8210/025-000	PFC200 G2 4ETH T	X	X
750-8210/040-000	PFC200 G2 4ETH XTR	X	X
750-8211	PFC200 G2 2ETH 2SFP	X	X
750-8211/040-000	PFC200 G2 2ETH 2SFP T	X	X
750-8211/040-001	PFC200 G2 2ETH 2SFP Tele T	X	X
750-8212	PFC200 G2 2ETH RS	X	X
750-8212/000-100	PFC200 G2 2ETH RS BACnet/IP		X
750-8212/025-000	PFC200 G2 2ETH RS T	X	X
750-8212/025-001	PFC200 G2 2ETH RS Tele T	X	X
750-8212/025-002	PFC200 G2 2ETH RS ECO Tele T	X	X
750-8212/040-000	PFC200 G2 2ETH RS XTR	X	X
750-8212/040-001	PFC200 G2 2ETH RS Tele XTR	X	X
750-8212/040-010	PFC200 G2 2ETH M12 RS XTR	X	X
750-8213	PFC200 G2 2ETH CAN	X	X
750-8213/040-010	PFC200 G2 2ETH M12 CAN XTR	X	X
750-8214	PFC200 G2 2ETH RS CAN	X	X
750-8215	PFC200 G2 4ETH CAN USB		X
750-8216	PFC200 G2 2ETH RS CAN DPS	X	X
750-8216/025-000	PFC200 G2 2ETH RS CAN DPS T	X	X
750-8216/025-001	PFC200 G2 2ETH RS CAN DPS Tele T	X	X
750-8216/040-000	PFC200 G2 2ETH RS CAN DPS XTR	X	X
750-8217	PFC200 G2 2ETH RS 4G EU		X
750-8217/025-000	PFC200 G2 2ETH RS 4G EU T		X
750-8217/600-000	PFC200 G2 2ETH RS 4G Global		X
750-8217/625-000	PFC200 G2 2ETH RS 4G Global T		X

This firmware will be released via GitHub: <https://github.com/WAGO>

5.1 System

- [FIXED] WAT-34925 Extended HTTP security header options in lighttpd (X-Content-Type-Options, Referrer-Policy).
- [FIXED] WAT-34893 Fixed CVE-2022-0529 , CVE-2022-0530
- [FIXED] WAT-34885 Updates libcurl to version 7.84.0; Fixes CVE-2022-22576 , CVE-2022-27782, CVE-2022-30115, CVE-2022-27775, CVE-2022-27781, CVE-2022-27776, CVE-2022-27779, CVE-2022-27780, CVE-2022-27774, CVE-2022-32205, CVE-2022-32206, CVE-2022-32207, CVE-2022-32208
- [FIXED] SECURITY CVE-2022-45137, CVE-2022-45139, CVE-2022-45140
- [FIXED] WAT-34878 Fix timing problem in SIM card detection after modem restart

-
- | | | |
|---------|-----------|---|
| [FIXED] | WAT-34828 | It is possible to downgrade to a hardened FW-Image without network connection lost. |
| [FIXED] | WAT-34356 | WBM Modem configuration (e.g. APN) allows special characters now |
| [FIXED] | WAT-34878 | Fix timing problem in SIM card detection after modem restart |

5.2 Operating System

- | | | |
|---------|-----------|---|
| [FIXED] | WAT-35076 | Fixed CVE-2022-40476 |
| [FIXED] | WAT-35071 | Fixed CVE-2022-2905 |
| [FIXED] | WAT-34965 | Updated expat to 2.4.9 (fixes CVE-2022-40674) |
| [FIXED] | WAT-34932 | MAC Address filter was active by default, from now on it is off as default (cf. IP firewall). |
| [FIXED] | WAT-34930 | Updated OpenLDAP to V2.6.2 (fixes CVE-2022-29155) |
| [FIXED] | WAT-34929 | Fixed CVE-2022-2097 (update OpenSSL to 1.1.1q) |
| [FIXED] | WAT-34926 | Fixed CVE-2022-0547 (OpenVPN) |
| [FIXED] | WAT-34920 | Fixed CVE-2022-1671 |
| [FIXED] | WAT-34918 | Fixed CVE-2021-33656, CVE-2022-2327, CVE-2022-36879, CVE-2022-1671 |
| [FIXED] | WAT-34917 | Fixed CVE-2021-33656, CVE-2022-2327, CVE-2022-36879, CVE-2022-1671 |
| [FIXED] | WAT-34915 | Fixed CVE-2022-34495 |
| [FIXED] | WAT-34914 | Fixed CVE-2022-34494, |
| [FIXED] | WAT-34913 | Fixed CVE-2022-1998 |
| [FIXED] | WAT-34911 | Fixed CVE-2022-29581 |
| [FIXED] | WAT-34910 | Fixed CVE-2022-32250 |
| [FIXED] | WAT-34908 | Fixed CVE-2022-32296 |
| [FIXED] | WAT-34906 | Fixed CVE-2022-30594 |
| [FIXED] | WAT-34905 | Fixed CVE-2022-1353 |
| [FIXED] | WAT-34904 | Fixed CVE-2022-1048 |
| [FIXED] | WAT-34902 | Fixed CVE-2022-29968 |
| [FIXED] | WAT-34900 | Fixed CVE-2022-29582 |
| [FIXED] | WAT-34899 | Fixed CVE-2021-45868, CVE-2022-27666 |
| [FIXED] | WAT-34898 | Fixed CVE-2021-45868, CVE-2022-27666 |
| [FIXED] | WAT-34895 | Fixed CVE-2022-28391 |
| [FIXED] | WAT-34891 | Fixed error that prevents restore of system backup when Docker is activated. |
| [FIXED] | WAT-34889 | Updated zlib to V1.2.12 (fixes CVE-2022-37434) |
| [FIXED] | WAT-34888 | Updated libarchive to V3.6.1. |
-

-
- | | | |
|---------|-----------|---|
| [FIXED] | WAT-34887 | Updated libxml2 to V2.9.14 (fixes CVE-2022-29824)
Updated libxslt to V1.1.36 (fixes CVE-2022-29824) |
| [FIXED] | WAT-34886 | Updated ntfs-3g to V2022.05.17 (fixes CVE-2022-30788, CVE-2022-30789, CVE-2022-30783, CVE-2022-30785, CVE-2022-30786, CVE-2022-30784) |
| [FIXED] | WAT-34884 | MAC Address filter configuration is loaded at boot time not only in event of changed configuration. |
| [FIXED] | WAT-33700 | Fixed erroneous logrotate configuration which leads to crash of CODESYS runtime when OpenVPN is used. |
| [NEW] | WAT-34890 | Updated logrotate to version 3.20.1. |

5.3 Runtime System

- | | | |
|---------|-----------|---|
| [KNOWN] | WAT-35177 | "PLC load watchdog" might not work as expected: the plc load watchdog will detect (e.g. an endless loop) but the IEC task might not be stopped in any case. This might lead to a complete stop of the runtime process. As workaround and improve "hardening" of your IEC application we recommend to use an IEC Task watchdog on all your relevant IEC tasks in your IEC application. |
|---------|-----------|---|

5.4 Fieldbus Interface & Protocols

OPC UA

- | | | |
|---------|-----------|--------------------------------|
| [FIXED] | WAT-34744 | Fixed security issue in OPC UA |
|---------|-----------|--------------------------------|

5.5 Web Based Management

- | | | |
|---------|-----------|--|
| [FIXED] | WBM-6869 | Enhanced webserver security - check correct content type in request. |
| [FIXED] | WAT-34837 | Allow leading digits for host names. |
| [FIXED] | WAT-34741 | Backup and Restore is executable by user "root". |
| [NEW] | | SNMPv3: Add support for strong privacy and encryption.
Authentication: SHA224, SHA256, SHA384, SHA512
Encryption: AES128, AES192, AES192C, AES256, AES256C |

5.6 Functional change

- | | | |
|--------------|--|--|
| [DEPRECATED] | | Config tool function get_telecontrol_state will be removed in future releases. |
|--------------|--|--|

The config tool was used to determine whether a device is a telecontrol. Since telecontrol services can be added by dynamic licensing, the tool is no longer needed.

[DEPRECATED]

DHCP and DNS Server will be removed in future releases.

For the transition, it will be included for now. In the next release, the servers will still be part of the firmware.

[REMOVED]

No more unauthenticated guest access possible in WBM.
No more unauthenticated configtool call possible via WBM HTTP/HTTPS interface.

5.7 Beta functionalities

[BETA]

"Wago Device Access" for parametrization and configuration.

The service is available and can already be tested. Changes in the model and behavior are possible for future versions.

REST-API is active under path "<host>/wda" on port 443.
File-Access-API is active under path "<host>/files" on port 443.

To disable the service, delete symlink "/etc/rc.d/S11_paramd" or move it to subdirectory "disabled".

Compared to the last firmware, many more parameter providers have been added.

[BETA]

A documentation for the REST-API of "Wago Device Access" is available from device by calling specified URL:
OpenAPI-JSON: <ip/hostname>/openapi/wda.openapi.json
HTML format: <ip/hostname>/openapi/wda.openapi.html

6 Firmware Release 03.10.08 (22) – e!COCKPIT and CODESYS 2

BUG FIX

SECURITY RELEVANT

NEW FEATURES

Compatible from e!COCKPIT Version	1.11	Compatible from WAGO I/O PRO Version	2.3.9.61
-----------------------------------	------	--------------------------------------	----------

Starting with firmware 19, the PFC100 and the PFC200 of the first generation have their own image and release notes.

Affected articles/Available for		Supported PLC	
Article Number	Designation	CDS2.3	e!Runtime
750-8210	PFC200 G2 4ETH	X	X
750-8210/025-000	PFC200 G2 4ETH T	X	X

750-8210/040-000	PFC200 G2 4ETH XTR	X	X
750-8211	PFC200 G2 2ETH 2SFP	X	X
750-8211/040-000	PFC200 G2 2ETH 2SFP T	X	X
750-8211/040-001	PFC200 G2 2ETH 2SFP Tele T	X	X
750-8212	PFC200 G2 2ETH RS	X	X
750-8212/000-100	PFC200 G2 2ETH RS BACnet/IP		X
750-8212/025-000	PFC200 G2 2ETH RS T	X	X
750-8212/025-001	PFC200 G2 2ETH RS Tele T	X	X
750-8212/025-002	PFC200 G2 2ETH RS ECO Tele T	X	X
750-8212/040-000	PFC200 G2 2ETH RS XTR	X	X
750-8212/040-001	PFC200 G2 2ETH RS Tele XTR	X	X
750-8212/040-010	PFC200 G2 2ETH M12 RS XTR	X	X
750-8213	PFC200 G2 2ETH CAN	X	X
750-8213/040-010	PFC200 G2 2ETH M12 CAN XTR	X	X
750-8214	PFC200 G2 2ETH RS CAN	X	X
750-8215	PFC200 G2 4ETH CAN USB		X
750-8216	PFC200 G2 2ETH RS CAN DPS	X	X
750-8216/025-000	PFC200 G2 2ETH RS CAN DPS T	X	X
750-8216/025-001	PFC200 G2 2ETH RS CAN DPS Tele T	X	X
750-8216/040-000	PFC200 G2 2ETH RS CAN DPS XTR	X	X
750-8217	PFC200 G2 2ETH RS 4G EU		X
750-8217/025-000	PFC200 G2 2ETH RS 4G EU T		X
750-8217/600-000	PFC200 G2 2ETH RS 4G Global		X
750-8217/625-000	PFC200 G2 2ETH RS 4G Global T		X

This firmware will be released via GitHub: <https://github.com/WAGO>

6.1 System

- [NEW] WAT-34301 Updated lighttpd to version 1.4.64
Updated PHP to version 7.4.28
- [NEW] WAT-34555 Allow to specify NTP server via hostname (additional to IP address)
- [NEW] WAT-34471 Updated ca-certificates to version NSS_3_78_RTM
- [NEW] It is possible to disable access to WBM while WebVisu is still available.
WAGO Device Access Service is necessary to enable or disable Web Based Management.
- [NEW] WAT-26465 Allow to configure NTP servers by hostname also (previously only IP addresses were allowed).
- [FIXED] WAT-34341 OpenSSL updated to 1.1.1n
- [FIXED] WAT-34439 Fixed CVE-2021-29155
- [FIXED] WAT-34387 Fixed data race during restore (WAGOupload failed to complete restore during controller reboot).
- [FIXED] WAT-34291 Updated libxml2 to 2.9.13 (fixes CVE-2022-23308)
- [FIXED] WAT-34290 Updated expat to 2.4.7 (fixes CVE-2022-25235, CVE-2022-25236, CVE-2022-25313, CVE-2022-25314, CVE-2022-25315)
- [FIXED] WAT-34185 Fixed integer in XML_GetBuffer
- [FIXED] WAT-30029 8217 Modem Parameter for Network Selection is not in PFC Settings Backup & Restore

6.2 Operating System

- [NEW] Updated Kernel to version 5.15 (LTS). Fixes CVE-2022-23222.
- [FIXED] WAT-34342 Fixed CVE-2021-4023, CVE-2021-3732
- [FIXED] WAT-34284 Fixed CVE-2022-0847
- [FIXED] WAT-34508 Fixed CVE-2021-22600
- [FIXED] WAT-34402 Fixed CVE-2021-4150, CVE-2021-4148, CVE-2021-4197, CVE-2022-0995
- [FIXED] WAT-34397 Fixed CVE-2021-45868, CVE-2022-27666

6.3 Runtime System

- [NEW] eIRUNTIME Upgrade to version 3.5.17.3 (based on CODESYS 3.5, SP 17, Patch 3)
Fixed CVE-2021-29242, CVE-2021-36765, CVE-2021-33485, CVE-2021-36763, CVE-2021-36764, CVE-2022-1989

6.4 Fieldbus Interface & Protocols

CAN

- [FIXED] WAT-34398 PFC CANopen Slave sends no heartbeat when bus detection fails

6.5 Web Based Management

- [NEW] root now has the same access rights to WBM like user "admin". By login with username "root", the user can change the password of linux user root and is not in need to change root password via SSH.

For security reasons, only users which are part of a WBM user group are able to access WBM. All other users will be rejected at WBM login.

- [NEW] WBM provides information about the used trademarks.
- [NEW] Force booting from the internal flash only and prohibit booting from SD card.

Notice: if you force booting from internal flash, an update is only possible via ETHERNET. There is a risk that you will no longer be able to connect to the device if there are any problems.

- [FIXED] WAT-34138 No Cross-site Scripting via wrong configtool name.
- [FIXED] WAT-32553 Enhanced user guidance and error message in case of wrong/missing label text while creating new filesystem on memory card.

6.6 Functional change

- [CHANGED] The Fast Aging function has been replaced by the MAC Learning function. A device with MAC Learning enabled on all ethernet interfaces behaves in the same way as a device with Fast Aging disabled behaved in the past. NEW: MAC Learning is also available on all 4-port devices (0750-8210, 750-8211 and 750-8215).
- [CHANGED] WBM - "Information": Remove display of "Serial Number", show "Unique Item Identifier (UII)" instead (only on devices which deliver an UII).
- [CHANGED] Update of the Sparkplug integration supporting Sparkplug devices connected to a Sparkplug node. IEC library seperated from Wago-AppCloud to WagoAppSparkplug. ATTENTION: Incompatible to previous version. Existing projects need to be adapted manually.
- [DEPRECATED] Config tool function `get_telecontrol_state` will be removed in future releases.
- The config tool was used to determine whether a device is a telecontrol. Since telecontrol services can be added by dynamic licensing, the tool is no longer needed.
- [DEPRECATED] DHCP and DNS Server will be removed in future releases.

For the transition, it will be included for now. In the next release, the servers will still be part of the firmware.

6.7 Beta functionalities

- [BETA] "Wago Device Access" for parametrization and configuration.
- The service is available and can already be tested. Changes in the model and behavior are possible for future versions.

REST-API is active under path "<host>/wda" on port 443.
File-Access-API is active under path "<host>/files" on port 443.

To disable the service, delete symlink "/etc/rc.d/S11_paramd" or move it to subdirectory "disabled".

Compared to the last firmware, many more parameter providers have been added.

[BETA]

A documentation for the REST-API of "Wago Device Access" is available from device by calling specified URL:
OpenAPI-JSON: <ip/hostname>/openapi/wda.openapi.json
HTML format: <ip/hostname>/openapi/wda.openapi.html

The Release Note(s) and the corresponding update(s) are provided free of charge. The statutory warranty and liability regulations of §§ 521, 523 BGB apply to possible errors in the Release Note(s) or possible defects in the update (CISG is excluded). The update(s) is (are) intended to further enhance and / or to enrich our product(s), but does not mean that the previous software version was defective. In order to benefit from the improvements, we generally recommend the implementation of the update(s), but we cannot assume the final responsibility for the installation of the update(s) or their costs. Since we know neither the concrete application nor the individual conditions of use.

7 Firmware Release 03.09.05 (21) – e!COCKPIT and CODESYS 2

BUG FIX

SECURITY RELEVANT

Compatible from e!COCKPIT Version	1.10*	Compatible from WAGO I/O PRO Version	2.3.9.61
* Service Pack 2 (2021-12) required			

Starting with firmware 19, the PFC100 and the PFC200 of the first generation have their own image and release notes.

Affected articles/Available for		Supported PLC	
Article Number	Designation	CDS2.3	e!Runtime
750-8210	PFC200 G2 4ETH	X	X
750-8210/025-000	PFC200 G2 4ETH T	X	X
750-8210/040-000	PFC200 G2 4ETH XTR	X	X
750-8211	PFC200 G2 2ETH 2SFP	X	X
750-8211/040-000	PFC200 G2 2ETH 2SFP T	X	X
750-8211/040-001	PFC200 G2 2ETH 2SFP Tele T	X	X
750-8212	PFC200 G2 2ETH RS	X	X
750-8212/000-100	PFC200 G2 2ETH RS BACnet/IP		X
750-8212/025-000	PFC200 G2 2ETH RS T	X	X
750-8212/025-001	PFC200 G2 2ETH RS Tele T	X	X
750-8212/025-002	PFC200 G2 2ETH RS ECO Tele T	X	X
750-8212/040-000	PFC200 G2 2ETH RS XTR	X	X
750-8212/040-001	PFC200 G2 2ETH RS Tele XTR	X	X

750-8212/040-010	PFC200 G2 2ETH M12 RS XTR	X	X
750-8213	PFC200 G2 2ETH CAN	X	X
750-8213/040-010	PFC200 G2 2ETH M12 CAN XTR	X	X
750-8214	PFC200 G2 2ETH RS CAN	X	X
750-8215	PFC200 G2 4ETH CAN USB		X
750-8216	PFC200 G2 2ETH RS CAN DPS	X	X
750-8216/025-000	PFC200 G2 2ETH RS CAN DPS T	X	X
750-8216/025-001	PFC200 G2 2ETH RS CAN DPS Tele T	X	X
750-8216/040-000	PFC200 G2 2ETH RS CAN DPS XTR	X	X
750-8217	PFC200 G2 2ETH RS 4G EU		X
750-8217/025-000	PFC200 G2 2ETH RS 4G EU T		X
750-8217/600-000	PFC200 G2 2ETH RS 4G Global		X
750-8217/625-000	PFC200 G2 2ETH RS 4G Global T		X

This firmware will be released via GitHub: <https://github.com/WAGO>

7.1 System

[FIXED] WAT34284 "Dirty Pipe" enables root privileges
CVE-2022-0847

7.2 Fieldbus Interface & Protocols

[FIXED] WAT33430 New e!Cockpit projects for 750-8217 automatically contains WagoSysModem as required library

8 Firmware Release 03.09.04 (21) – e!COCKPIT and CODESYS 2

BUG FIX

SECURITY RELEVANT

NEW FEATURES

Compatible from e!COCKPIT Version	1.10*	Compatible from WAGO I/O PRO Version	2.3.9.61
* Service Pack 2 (2021-12) required			

Starting with firmware 19, the PFC100 and the PFC200 of the first generation have their own image and release notes.

FW not for 750-8217 usable.

Affected articles/Available for		Supported PLC	
Article Number	Designation	CDS2.3	e!Runtime
750-8210	PFC200 G2 4ETH	X	X
750-8210/025-000	PFC200 G2 4ETH T	X	X
750-8210/040-000	PFC200 G2 4ETH XTR	X	X
750-8211	PFC200 G2 2ETH 2SFP	X	X
750-8211/040-000	PFC200 G2 2ETH 2SFP T	X	X
750-8211/040-001	PFC200 G2 2ETH 2SFP Tele T	X	X
750-8212	PFC200 G2 2ETH RS	X	X
750-8212/000-100	PFC200 G2 2ETH RS BACnet/IP		X
750-8212/025-000	PFC200 G2 2ETH RS T	X	X
750-8212/025-001	PFC200 G2 2ETH RS Tele T	X	X
750-8212/025-002	PFC200 G2 2ETH RS ECO Tele T	X	X
750-8212/040-000	PFC200 G2 2ETH RS XTR	X	X
750-8212/040-001	PFC200 G2 2ETH RS Tele XTR	X	X
750-8212/040-010	PFC200 G2 2ETH M12 RS XTR	X	X
750-8213	PFC200 G2 2ETH CAN	X	X
750-8213/040-010	PFC200 G2 2ETH M12 CAN XTR	X	X

750-8214	PFC200 G2 2ETH RS CAN	X	X
750-8215	PFC200 G2 4ETH CAN USB		X
750-8216	PFC200 G2 2ETH RS CAN DPS	X	X
750-8216/025-000	PFC200 G2 2ETH RS CAN DPS T	X	X
750-8216/025-001	PFC200 G2 2ETH RS CAN DPS Tele T	X	X
750-8216/040-000	PFC200 G2 2ETH RS CAN DPS XTR	X	X
750-8217	PFC200 G2 2ETH RS 4G EU		X
750-8217/025-000	PFC200 G2 2ETH RS 4G EU T		X
750-8217/600-000	PFC200 G2 2ETH RS 4G Global		X
750-8217/625-000	PFC200 G2 2ETH RS 4G Global T		X

This firmware will be released via GitHub: <https://github.com/WAGO>

8.1 System

- [NEW] WAT32833 Improved robustness of application control with operating mode switch and additional detection of invalid states.
- [NEW] IP forwarding is activated implicitly when Docker is activated.
- [NEW] WAT34079 Libcurl update to version 7.81.0
- [NEW] Bootloader update to version 2021.10.0
- [FIXED] WAT33827 Sender of SNMP "Informs" could be changed
- [FIXED] WAT33547 deactivate Multicast Snooping by default
- [FIXED] WAT33914 4-Port PFCs now forwarding BPDU packets
- [FIXED] WAT34053 Security-Fix in config-tool print_log.
- [FIXED] WAT34123 Network bridges discard their IP address when all associated network ports are disconnected.
- [FIXED] WAT34284 "Dirty Pipe" enables root privileges
CVE-2022-0847

8.2 Fieldbus Interface & Protocols

OPC UA

- [NEW] OPC UA client that can establish a connection to an OPC UA server via standardized PLCopen function blocks.

CAN

- [FIXED] WAT34135 CAN interface goes into BusOff by TxOverflow

BACnet

[NEW] The BACnet revision has been updated from revision 14 to revision 22

Cloud

[NEW] Proxy configuration for MS Azure + Wago Cloud in WBM configurable

8.3 Functional change

[DEPRECATED] Config tool function `get_telecontrol_state` will be removed in future releases.

The config tool was used to determine whether a device is a telecontrol. Since telecontrol services can be added by dynamic licensing, the tool is no longer needed.

[DEPRECATED] DHCP and DNS Server will be removed in future releases.

For the transition, it will be included for now. In the next release, the servers will still be part of the firmware.

8.4 Beta functionalities

[BETA] "Wago Device Access" for parametrization and configuration.

The service is available and can already be tested. Changes in the model and behavior are possible for future versions.

REST-API is active under path "`<host>/wda`" on port 443.
File-Access-API is active under path "`<host>/files`" on port 443.

To disable the service, delete symlink "`/etc/rc.d/S11_paramd`" or move it to subdirectory "disabled".

Compared to the last firmware, many more parameter providers have been added.

The Release Note(s) and the corresponding update(s) are provided free of charge. The statutory warranty and liability regulations of §§ 521, 523 BGB apply to possible errors in the Release Note(s) or possible defects in the update (CISG is excluded). The update(s) is (are) intended to further enhance and / or to enrich our product(s), but does not mean that the previous software version was defective. In order to benefit from the improvements, we generally recommend the implementation of the update(s), but we cannot assume the final responsibility for the installation of the update(s) or their costs. Since we know neither the concrete application nor the individual conditions of use.

9 Firmware Release 03.08.08 (20)

BUG FIX

SECURITY RELEVANT

NEW HARDWARE

NEW FEATURES

Compatible from e!COCKPIT Version	1.10*	Compatible from WAGO I/O PRO Version	2.3.9.61
-----------------------------------	-------	--------------------------------------	----------

* Service Pack 1 (2021-12) required

This firmware will be released via GitHub: <https://github.com/WAGO>

9.1 System

[FIXED] WAT33793 IPsec: SHA512 based ESP algorithms not available.

9.2 Fieldbus Interface & Protocols

[FIXED] WAT33827 Sender of SNMP "Informs" not changeable via IEC Libraries.

The Release Note(s) and the corresponding update(s) are provided free of charge. The statutory warranty and liability regulations of §§ 521, 523 BGB apply to possible errors in the Release Note(s) or possible defects in the update (CISG is excluded). The update(s) is (are) intended to further enhance and / or to enrich our product(s), but does not mean that the previous software version was defective. In order to benefit from the improvements, we generally recommend the implementation of the update(s), but we cannot assume the final responsibility for the installation of the update(s) or their costs. Since we know neither the concrete application nor the individual conditions of use.

10 Firmware Release 03.08.07 (20)

SECURITY RELEVANT

NEW HARDWARE

NEW FEATURES

Compatible from e!COCKPIT Version	1.10*	Compatible from WAGO I/O PRO Version	2.3.9.61
-----------------------------------	-------	--------------------------------------	----------

* Service Pack 1 (2021-12) required

Starting with firmware 19, the PFC100 and the PFC200 of the first generation have their own image and release notes.

Affected articles/Available for		Supported PLC	
Article Number	Designation	CDS2.3	e!Runtime
750-8210	PFC200 G2 4ETH	X	X
750-8210/025-000	PFC200 G2 4ETH T	X	X
750-8210/040-000	PFC200 G2 4ETH XTR	X	X
750-8211	PFC200 G2 2ETH 2SFP	X	X
750-8211/040-000	PFC200 G2 2ETH 2SFP T	X	X
750-8211/040-001	PFC200 G2 2ETH 2SFP Tele T	X	X
750-8212	PFC200 G2 2ETH RS	X	X
750-8212/000-100	PFC200 G2 2ETH RS BACnet/IP		X
750-8212/025-000	PFC200 G2 2ETH RS T	X	X
750-8212/025-001	PFC200 G2 2ETH RS Tele T	X	X
750-8212/025-002	PFC200 G2 2ETH RS ECO Tele T	X	X
750-8212/040-000	PFC200 G2 2ETH RS XTR	X	X
750-8212/040-001	PFC200 G2 2ETH RS Tele XTR	X	X
750-8212/040-010	PFC200 G2 2ETH M12 RS XTR	X	X
750-8213	PFC200 G2 2ETH CAN	X	X
750-8213/040-010	PFC200 G2 2ETH M12 CAN XTR	X	X
750-8214	PFC200 G2 2ETH RS CAN	X	X
750-8215	PFC200 G2 4ETH CAN USB		X
750-8216	PFC200 G2 2ETH RS CAN DPS	X	X
750-8216/025-000	PFC200 G2 2ETH RS CAN DPS T	X	X
750-8216/025-001	PFC200 G2 2ETH RS CAN DPS Tele T	X	X
750-8216/040-000	PFC200 G2 2ETH RS CAN DPS XTR	X	X
750-8217	PFC200 G2 2ETH RS 4G EU		X
750-8217/025-000	PFC200 G2 2ETH RS 4G EU T		X
750-8217/600-000	PFC200 G2 2ETH RS 4G Global		X
750-8217/625-000	PFC200 G2 2ETH RS 4G Global T		X

This firmware will be released via GitHub: <https://github.com/WAGO>

10.1 System

[NEW] Integration of Docker Deamon. Docker now can be installed and activated via. WBM.

[NEW] Users of WBM and Linux where harmonized.

User "user" and "admin" can still be used for authorization in WBM as default, but they are no longer exclusive for WBM.

Every WBM user can only change his own password now.

To use WBM, linux user can be added to group "wbm-admin" or "wbm-user". All other users where treated as "guest".

Note:

Configuration/change of password in WBM will directly change the configuration of the corresponding linux user and vice versa.

After upgrade to FW 20, login in WBM is not possible with the old WBM passwords; you must use the passwords of the corresponding linux users.

After a following downgrade to FW 19 (or less), WBM will use the WBM default passwords.

[NEW] "Codesys port authentication password" can no longer be changed via WBM.

[NEW] From FW20 the HTTPS port is always active and cannot be disabled via WBM or configtool. Please note that this will be the state after a firmware update, regardless which state was configured before. If necessary, the HTTPS port can be blocked via the firewall.

[NEW] PTXdist update to version 2020.8.0

[NEW] openssl update to version 1.1.1.L

[NEW] WAT33917 Busybox update to version 1.34.1

CVE-2021-42378, CVE-2021-42379, CVE-2021-42380, CVE-2021-42381, CVE-2021-42382, CVE-2021-42383, CVE-2021-42384, CVE-2021-42385, CVE-2021-42386

[FIXED] PFC200 with 4G: Fix issue with sporadic high system load leading to a KBus watchdog timeout when modem starts unexpected re-initialisation of SIM card in operational state.

[KNOWN] WAT33180 PFC200 with 4G: 2kB Memoryleak for each Modem-Reset.
10.1.1

10.2 Runtime System

[FIXED] WAT33476 Fix possible deadlock when using multiple tasks in an e!Cockpit application on PFC based controllers leading to a KBus watchdog timeout (signalled by IO LED error blinkcode 9-5)

[FIXED] Fixed CODESYS 2.3 webserver vulnerabilities regarding CODESYS advisory 2021-15_LCDS-358: CVE-2021-34583, CVE-2021-34584, CVE-2021-34585, CVE-2021-34586

[FIXED] Fixed CODESYS 2.3 runtime vulnerability regarding CODESYS advisory 2021-16_LCDS-361: CVE-2021-34593

[FIXED] Fixed CODESYS 2.3 runtime vulnerabilities regarding CODESYS advisory 2021-17_LCDS-362: CVE-2021-34595, CVE-2021-34596

10.3 Fieldbus Interface & Protocols

OPC UA

[FIXED] WAT32891 The OPC UA port is now correctly opened in the firewall after restart.

CAN

[NEW] It is now possible to use extended CAN configuration in e!COCKPIT

BACnet

[FIXED] WAT33683 When using BACnet, there is no longer an increase in open file descriptors.

Cloud Connectivity

[NEW] Cloud Connectivity: Update Azure SDK to 1.6.0

10.4 Functional change

[DEPRECATED] Config tool function `get_telecontrol_state` will be removed in future releases.

The config tool was used to determine whether a device is a telecontrol. Since telecontrol services can be added by dynamic licensing, the tool is no longer needed.

[REMOVED] Removed Telnet server, use SSH instead.

[REMOVED] Removed TFTP server.

10.5 Beta functionalities

[BETA] "Wago Device Access" for parametrization and configuration.

The service is available and can already be tested. Changes in the model and behavior are possible for future versions.

REST-API is active under path "`<host>/wda`" on port 443.
File-Access-API is active under path "`<host>/files`" on port 443.

To disable the service, delete symlink "`/etc/rc.d/S11_paramd`" or move it to subdirectory "disabled".

The Release Note(s) and the corresponding update(s) are provided free of charge. The statutory warranty and liability regulations of §§ 521, 523 BGB apply to possible errors in the Release Note(s) or possible defects in the update (CISG is excluded). The update(s) is (are) intended to further enhance and / or to enrich our product(s), but does not mean that the previous software version was defective. In order to benefit from the improvements, we generally recommend the implementation of the update(s), but we cannot assume the final responsibility for the installation of the update(s) or their costs. Since we know neither the concrete application nor the individual conditions of use.

11 Firmware Release 03.07.14 (19)

SECURITY RELEVANT

NEW HARDWARE

NEW FEATURES

Compatible from e!COCKPIT Version	1.9*	Compatible from WAGO I/O PRO Version	2.3.9.61
-----------------------------------	------	--------------------------------------	----------

* Service Pack 1 (2021-08) required

Starting with firmware 19, the PFC100 and the PFC200 of the first generation have their own image and release notes.

Affected articles/Available for		Supported PLC	
Article Number	Designation	CDS2.3	e!Runtime
750-8210	PFC200 G2 4ETH	X	X
750-8210/025-000	PFC200 G2 4ETH T	X	X
750-8210/040-000	PFC200 G2 4ETH XTR	X	X
750-8211	PFC200 G2 2ETH 2SFP	X	X
750-8211/040-000	PFC200 G2 2ETH 2SFP T	X	X
750-8211/040-001	PFC200 G2 2ETH 2SFP Tele T	X	X
750-8212	PFC200 G2 2ETH RS	X	X
750-8212/000-100	PFC200 G2 2ETH RS BACnet/IP		X
750-8212/025-000	PFC200 G2 2ETH RS T	X	X
750-8212/025-001	PFC200 G2 2ETH RS Tele T	X	X
750-8212/025-002	PFC200 G2 2ETH RS ECO Tele T	X	X
750-8212/040-000	PFC200 G2 2ETH RS XTR	X	X
750-8212/040-001	PFC200 G2 2ETH RS Tele XTR	X	X
750-8212/040-010	PFC200 G2 2ETH M12 RS XTR	X	X
750-8213	PFC200 G2 2ETH CAN	X	X
750-8213/040-010	PFC200 G2 2ETH M12 CAN XTR	X	X
750-8214	PFC200 G2 2ETH RS CAN	X	X
750-8215	PFC200 G2 4ETH CAN USB		X
750-8216	PFC200 G2 2ETH RS CAN DPS	X	X
750-8216/025-000	PFC200 G2 2ETH RS CAN DPS T	X	X
750-8216/025-001	PFC200 G2 2ETH RS CAN DPS Tele T	X	X
750-8216/040-000	PFC200 G2 2ETH RS CAN DPS XTR	X	X
750-8217	PFC200 G2 2ETH RS 4G EU		X
750-8217/025-000	PFC200 G2 2ETH RS 4G EU T		X
750-8217/600-000	PFC200 G2 2ETH RS 4G Global		X
750-8217/625-000	PFC200 G2 2ETH RS 4G Global T		X

This firmware will be released via GitHub: <https://github.com/WAGO>

11.1 System

- [NEW] Extend routing functionality: routing over an interface.
- [NEW] WAT25306 The configuration of a default gateway can now be set on the TCP/IP configuration page in the WBM together with the IP configuration.
- [NEW] WAT32943 Extend the Fix-IP-Feature to address all configured bridges. (Not only bridge 0)
- [NEW] Updated kernel to version 5.10
- [FIXED] WAT22710 SEC: Disabled local and remote port forwarding for SSH server by default (conforming to in BDEW whitepaper)
- [FIXED] WAT27285 Fixed invalid progress of 30% during firmware update.
- [FIXED] WAT32419 Prevent dropbear from logging "no such file or directory"
- [FIXED] WAT33149 Allow PN connection up to 64 modules.
- WAT30279
- [FIXED] WAT32675 Fix synchronisation error while using WagoLibNetSnmpManager and WagoLibNetSnmp.
- [FIXED] WAT28783 PFC is not sending coldstart trap via SNMP
- [FIXED] WAT27060 WagoConfigToolLib could not be used to read DHCP assignees DNS server and default gateway
- [FIXED] WAT32606 Fix port mirroring visualisation error in WBM.
- WAT32832
- [FIXED] SEC: Updated dnsmasq to 2.83; Fixed CVE-2020-25684, CVE-2020-25685, CVE-2020-25686
- [FIXED] SEC: Updated sudo to 1.9.5p2; Addresses CVE-2021-3156
- [FIXED] WAT32065 Fixed issue displaying the wrong timezone after select timezone CET via WBM.
- [FIXED] WAT32817 Fix SNMP v2c Inform Notification function (extend FB)
- [FIXED] Updated ca-certificates to NSS.3.60.1.RTM
- [FIXED] WAT33002 Updated webserver lighttpd to version 1.4.59
- [FIXED] WAT32618 DRM evaluation mode is not signaled by SYS-LED for firmware functions that needs a license (e.g. Multi-Cloud, BACnet)
- [FIXED] WAT33412 Fix temporary network loop/network bridge within the FW update process, if the network is separated and connected to more than one network
- [KNOWN] WAT33180 PFC200 with 4G: 2kB Memoryleak for each Modem-Reset.

11.1.1

11.2 Runtime System

- [NEW] e!RUNTIME Upgrade to version 3.5.16.3 (based on CODESYS 3.5, SP 16, Patch 3)
- [FIXED] WAT31861 Bootproject with e!Cockpit application doesn't start when using retain variables and changing application without download.
- [FIXED] WAT31959
- [FIXED] WAT33491 CODESYS2 WebVisu doesn't show variable values when port authentication is enabled since FW18 Patch3

11.3 Fieldbus Interface & Protocols

OPC UA

- [FIXED] The OPC UA port is now correctly opened in the firewall.

Modbus

- [NEW] Bidirectional access to address ranges adjustable
- [FIXED] WAT33049 Fix Modbus Master (Client) mode OnValueChanged to write data in Modbus Slave (Server) registers.
- WAT33166

CAN

- [FIXED] WAT-32262 PFC sends unexpected CAN emergency telegram.
- [FIXED] WAT-32399 CAN layer2 receive does not work when calling FbCanL2Open in each SPS cycle.
- [FIXED] WAT-32995 CAN layer2 keeps sockets open / memory leak
- [FIXED] WAT-32771 CAN layer2 memory leak when opening CAN socket in disconnected state

BACnet

- [NEW] All log files under /var/log can be selected and displayed on the WBM Diagnostic page. The guest user is excluded

Cloud Connectivity

- [NEW] Add support for cache mode SD-Card for NativeMQTT
- [NEW] IEC retain data is not deleted during transfer of boot application. Retain data may be reused if it is still compatible to boot application.
- [FIXED] Use exponential backoff for retry interval if connection fails due to failing certificate validation

11.4 Libraries

- [FIXED] WAT-33313 Set path to standard certificate store (/etc/ssl/certs) for curl library.
- [FIXED] WAT-32886 Restore behavior of WagoSysProcess library for PFC firmware release 17 and older.

11.5 Functional change

- [DEPRECATED] Config tool function `get_telecontrol_state` will be removed in future releases.
- The config tool was used to determine whether a device is a telecontrol. Since telecontrol services can be added by dynamic licensing, the tool is no longer needed.
- [REMOVED] 3S OPC UA Server removed from the firmware. (Can be installed for firmware 19, available via support: support@wago.com).
- [CHANGED] In future releases, HTTPS-Port is always active and can only be switched off by the firewall.

The Release Note(s) and the corresponding update(s) are provided free of charge. The statutory warranty and liability regulations of §§ 521, 523 BGB apply to possible errors in the Release Note(s) or possible defects in the update (CISG is excluded). The update(s) is (are) intended to further enhance and / or to enrich our product(s), but does not mean that the previous software version was defective. In order to benefit from the improvements, we generally recommend the implementation of the update(s), but we cannot assume the final responsibility for the installation of the update(s) or their costs. Since we know neither the concrete application nor the individual conditions of use.

12 Firmware Release 03.06.19 (18)

SECURITY RELEVANT

NEW FEATURES

Compatible from e!COCKPIT Version	1.8	Compatible from WAGO I/O PRO Version	2.3.9.61
-----------------------------------	-----	--------------------------------------	----------

This firmware will be released via GitHub: <https://github.com/WAGO>

12.1 System

- [NEW] PFC200 with 4G: Send and receive SMS via e!COCKPIT IEC-Library
- [NEW] PFC200 with 4G: Modem configuration can now be prepared in WBM even when SIM is not inserted or locked
- [NEW] PFC200 with 4G: Manual configuration of net type and provider via WBM
- [NEW] PFC200 with 4G: Networkscan of available mobile radio networks via WBM
- [NEW] PFC200 with 4G: CID/LAC to determine the location of the cell tower
- [FIXED] PFC200 with 4G: Stabilization for applications with massive cell changes
- [FIXED] WAT-32751 PFC200 with 4G: Authentication type "PAP or CHAP" can now be configured correctly

[KNOWN] PFC200 with 4G: 2kB Memoryleak for each Modem-Reset.

Attention!

To be able to use the new features for the PFC200 with 4G, e!COCKPIT v1.9 is required. In addition, a small change must be made in the Library Manager of the e!COCKPIT project. The placeholder WagoSysModem_Internal must be set to WagoSysModem_Internal_PFC_1.1.4.0.

12.2 Fieldbus Interface & Protocols

OPC UA

[FIXED] WAT-32826 Nested IEC structures are now supported

[NEW]

The Endpoint URL can be set in the WBM between the Hostname and the IP addresses of the bridges

StructureFields are now supported.

[NEW]

Structured DataType is used to provide the metadata for a field of a custom Structure DataType. (OPC UA Specification Part 3 - 8.51 StructureField)

Cloud Connectivity

[FIXED] CC-2133 Fixed issues which may lead to crash or deadlock of cloud connection.

[FIXED] CC-2247

native MQTT: Fixed blocked data transmission if more than 20 subscriptions are used and broker is not available during initial connect.

12.3 Runtime System

[NEW]

SEC, CDS2: CODESYS Advisory 2021-06 (Security update for CODESYS Control V2 communication)

[NEW]

SEC, CDS2: CODESYS Advisory 2021-07 (Security update for CODESYS V2 web server)

12.3.1

13 Firmware Release 03.06.11 (18)

BUG FIX

Compatible from e!COCKPIT Version	1.8	Compatible from WAGO I/O PRO Version	2.3.9.61
-----------------------------------	-----	--------------------------------------	----------

This firmware will be released via GitHub: <https://github.com/WAGO>

13.1 System

[FIXED] WAT32767 Fixed system freeze on frequent access to retain memory.

13.1.1

The Release Note(s) and the corresponding update(s) are provided free of charge. The statutory warranty and liability regulations of §§ 521, 523 BGB apply to possible errors in the Release Note(s) or possible defects in the update (CISG is excluded). The update(s) is (are) intended to further enhance and / or to enrich our product(s), but does not mean that the previous software version was defective. In order to benefit from the improvements, we generally recommend the implementation of the update(s), but we cannot assume the final responsibility for the installation of the update(s) or their costs. Since we know neither the concrete application nor the individual conditions of use.

14 Firmware Release 03.06.09 (18)

SECURITY RELEVANT

NEW HARDWARE

NEW FEATURES

Compatible from e!COCKPIT Version		1.8	Compatible from WAGO I/O PRO Version		2.3.9.61
Affected articles/Available for			Supported PLC		
Article Number	Designation		CDS2.3	e!Runtime	
750-8100	PFC100 2ETH ECO			X	
750-8101	PFC100 2ETH			X	
750-8101/025-000	PFC100 2ETH T			X	
750-8102	PFC100 2ETH RS			X	
750-8102/025-000	PFC100 2ETH RS T			X	
750-8101/000-010	PFC100 FG0 2ETH			X	
750-8202	PFC200 2ETH RS ^{2,3,4}		X	X	
750-8203	PFC200 2ETH CAN ^{2,3,4}		X	X	
750-8204	PFC200 2ETH RS CAN ^{2,3,4}		X	X	
750-8206	PFC200 2ETH RS CAN DPS ^{2,3,4}		X	X	
750-8207	PFC200 2ETH RS 3G ⁴		X	X	
750-8208	PFC200 2ETH RS CAN DPM ⁴		X		
750-8202/025-000	PFC200 2ETH RS T ^{2,3,4}		X	X	
750-8202/025-001	PFC200 2ETH RS Tele T ^{2,3,4}		X	(X) ¹	
750-8202/025-002	PFC200 2ETH RS ECO Tele T ^{2,3,4}		X	(X) ¹	
750-8203/025-000	PFC200 2ETH CAN T ^{2,3,4}		X	X	
750-8204/025-000	PFC200 2ETH RS CAN T ^{2,3,4}		X	X	
750-8206/025-000	PFC200 2ETH RS CAN DPS T ^{2,3,4}		X	X	
750-8206/025-001	PFC200 2ETH RS CAN DPS Tele T ^{2,3,4}		X	(X) ¹	
750-8207/025-000	PFC200 2ETH RS 3G T ⁴		X	X	
750-8207/025-001	PFC200 2ETH RS 3G Tele T ⁴		X	(X) ¹	
750-8208/025-000	PFC200 2ETH RS CAN DPM T ⁴		X		
750-8208/025-001	PFC200 2ETH RS CAN DPM Tele T ⁴		X		
750-8202/040-000	PFC200 2ETH RS XTR ⁴		X	X	
750-8202/040-001	PFC200 2ETH RS Tele XTR ⁴		X	(X) ¹	
750-8206/040-000	PFC200 2ETH RS CAN DPS XTR ⁴		X	X	
750-8206/040-001	PFC200 2ETH RS CAN DPS Tele XTR ⁴		X	(X) ¹	
750-8202/000-011	PFC200 FG1 2ETH RS ⁴		X	X	
750-8202/000-012	PFC200 FG2 2ETH RS ⁴		X	X	
750-8202/000-022	PFC200 FGE 2ETH RS ⁴		X	X	
750-8207/000-022	PFC200 FGE 2ETH RS 3G ⁴		X	X	
750-8210	PFC200 G2 4ETH		X	X	
750-8211	PFC200 G2 2ETH 2SFP		X	X	
750-8212	PFC200 G2 2ETH RS		X	X	

750-8213	PFC200 G2 2ETH CAN	X	X
750-8214	PFC200 G2 2ETH RS CAN	X	X
750-8215	PFC200 G2 4ETH CAN USB		X
750-8216	PFC200 G2 2ETH RS CAN DPS	X	X
750-8217	PFC200 G2 2ETH RS 4G		X
750-8210/025-000	PFC200 G2 4ETH T	X	X
750-8212/025-000	PFC200 G2 2ETH RS T	X	X
750-8212/025-001	PFC200 G2 2ETH RS Tele T	X	X
750-8212/025-002	PFC200 G2 2ETH RS ECO Tele T	X	X
750-8212/000-100	PFC200 G2 2ETH RS BACnet/IP		X
750-8216/025-000	PFC200 G2 2ETH RS CAN DPS T	X	X
750-8216/025-001	PFC200 G2 2ETH RS CAN DPS Tele T	X	X
750-8217/025-000	PFC200 G2 2ETH RS 4G T		X
750-8210/040-000	PFC200 G2 4ETH XTR	X	X
750-8211/040-000	PFC200 G2 2ETH 2SFP T	X	X
750-8211/040-001	PFC200 G2 2ETH 2SFP Tele T	X	X
750-8212/040-000	PFC200 G2 2ETH RS XTR	X	X
750-8212/040-001	PFC200 G2 2ETH RS Tele XTR	X	X
750-8212/040-010	PFC200 G2 2ETH M12 RS XTR	X	X
750-8213/040-010	PFC200 G2 2ETH M12 CAN XTR	X	X
750-8216/040-000	PFC200 G2 2ETH RS CAN DPS XTR	X	X

Important:

- 1 e!RUNTIME available for devices produced 07/2017 or later
- 2 Product discontinued, last call on 31.12.2020
- 3 Firmware is guaranteed to be maintained until the last FW release 2021
- 4 **New features not guaranteed for next firmware versions**

This firmware will be released via GitHub: <https://github.com/WAGO>

14.1 System

- [NEW] PFC200 with 4G: Modem reset possible
- [NEW] The invalid IP adress 0.0.0.0 is not accepted by the system.
- [NEW] In case of IP missconfiguration a corresponding error message is displayed in the WBM dialog.
- [NEW] Compiler Update to Linaro GCC 9.2
- [FIXED] WAT31972W AT32325 WBM: Not all TZ strings can be set and displayed
- [FIXED] WAT32141 Communication over service port could not established.
- [FIXED] WAT31951 750-8207: Connection problems with roaming SIM cards
- [FIXED] WAT32108 750-8212: Config tool bootproject argument not available
- [FIXED] WAT32262 PFC sends undocumented emergency telegram
- [REMOVED] Removed deprecated function ct_liblog_reportError

14.2 Runtime System

- [NEW] e!RUNTIME Upgrade to Version 3.5.15.4 (based on CODESYS 3.5, SP 15, Patch 4)
- [FIXED] WAT30855 RUN-LED stays red when application restarts itself
- [FIXED] WAT30841 Wrong time stamp for alarms.

14.3 Fieldbus Interface & Protocols

OPC UA		
[NEW]		Integration of the WAGO OPC UA server into the Firmware.
[NEW]		Import of a customer-specific information model possible. (WAGO Mapping Editor is required.)
[REMOVED]		Discontinue 3S OPC UA Server in the firmware. (Can be installed for firmware 19, available via support: support@wago.com).

CAN		
[FIXED]	WAT32038	CAN continues to run even if the Runtime crashes
[FIXED]	WAT31936	750-8215: Missing EDS file for CAN

BACnet		
[NEW]		BACnet S license added to the BACnet Stack.
[NEW]		BACnet: Added further error code information on incorrect user input.

Cloud Connectivity		
[NEW]		Cloud Connectivity: Use Azure specific system properties to provide content type and content encoding of device2cloud messages for message routing
[FIXED]		Cloud Connectivity: WBM: Minor usability issues
[FIXED]		Cloud Connectivity: Improve robustness in scenarios with high transmission rate and high data volume
[FIXED]		Cloud Connectivity: Resend DeviceHello message with interval of 30 seconds if corresponding CloudHello message is not received
[REMOVED]		Cloud Connectivity: Discontinue support of WAGO Protocol 1.0
[REMOVED]		Cloud Connectivity: Discontinue support of Cloud Connectivity with WagoLibCloud_02.lib for Codesys 2.3

SFTP		
[FIXED]	WAT31270	SFTP Client freezes

14.4 Libraries

[NEW]	WAT31930	Updated libssh (1.8.0 -> 1.9.0)
[NEW]		Library for monitoring and controlling the modem.
[FIXED]	WAT32098	CDS2 configToolFb is blocking while error handling.

The Release Note(s) and the corresponding update(s) are provided free of charge. The statutory warranty and liability regulations of §§ 521, 523 BGB apply to possible errors in the Release Note(s) or possible defects in the update (CISG is excluded). The update(s) is (are) intended to further enhance and / or to enrich our product(s), but does not mean that the previous software version was defective. In order to benefit from the improvements, we generally recommend the implementation of the update(s), but we cannot assume the final responsibility for the installation of the update(s) or their costs. Since we know neither the concrete application nor the individual conditions of use.

15 Firmware Release 03.05.10 (17)

Compatible from e!COCKPIT Version	1.7*	Compatible from WAGO I/O PRO Version	2.3.9.61
-----------------------------------	------	--------------------------------------	----------

* Service Pack 1 (2020-07) required

Affected articles/Available for		Supported PLC	
Article Number	Designation	CDS2.3	e!Runtime
750-8100	PFC100 2ETH ECO		X
750-8101	PFC100 2ETH		X
750-8101/025-000	PFC100 2ETH T		X
750-8102	PFC100 2ETH RS		X
750-8102/025-000	PFC100 2ETH RS T		X
750-8101/000-010	PFC100 FG0 2ETH		X
750-8202	PFC200 2ETH RS ^{2,3,4}	X	X
750-8203	PFC200 2ETH CAN ^{2,3,4}	X	X
750-8204	PFC200 2ETH RS CAN ^{2,3,4}	X	X
750-8206	PFC200 2ETH RS CAN DPS ^{2,3,4}	X	X
750-8207	PFC200 2ETH RS 3G ⁴	X	X
750-8208	PFC200 2ETH RS CAN DPM ⁴	X	
750-8202/025-000	PFC200 2ETH RS T ^{2,3,4}	X	X
750-8202/025-001	PFC200 2ETH RS Tele T ^{2,3,4}	X	(X) ¹
750-8202/025-002	PFC200 2ETH RS ECO Tele T ^{2,3,4}	X	(X) ¹
750-8203/025-000	PFC200 2ETH CAN T ^{2,3,4}	X	X
750-8204/025-000	PFC200 2ETH RS CAN T ^{2,3,4}	X	X
750-8206/025-000	PFC200 2ETH RS CAN DPS T ^{2,3,4}	X	X
750-8206/025-001	PFC200 2ETH RS CAN DPS Tele T ^{2,3,4}	X	(X) ¹
750-8207/025-000	PFC200 2ETH RS 3G T ⁴	X	X
750-8207/025-001	PFC200 2ETH RS 3G Tele T ⁴	X	(X) ¹
750-8208/025-000	PFC200 2ETH RS CAN DPM T ⁴	X	
750-8208/025-001	PFC200 2ETH RS CAN DPM Tele T ⁴	X	
750-8202/040-000	PFC200 2ETH RS XTR ⁴	X	X
750-8202/040-001	PFC200 2ETH RS Tele XTR ⁴	X	(X) ¹
750-8206/040-000	PFC200 2ETH RS CAN DPS XTR ⁴	X	X
750-8206/040-001	PFC200 2ETH RS CAN DPS Tele XTR ⁴	X	(X) ¹
750-8202/000-011	PFC200 FG1 2ETH RS ⁴	X	X
750-8202/000-012	PFC200 FG2 2ETH RS ⁴	X	X
750-8202/000-022	PFC200 FGE 2ETH RS ⁴	X	X
750-8207/000-022	PFC200 FGE 2ETH RS 3G ⁴	X	X
750-8210	PFC200 G2 4ETH	X	X
750-8212	PFC200 G2 2ETH RS	X	X
750-8213	PFC200 G2 2ETH CAN	X	X

750-8214	PFC200 G2 2ETH RS CAN	X	X
750-8215	PFC200 G2 4ETH CAN USB		X
750-8216	PFC200 G2 2ETH RS CAN DPS	X	X
750-8217	PFC200 G2 2ETH RS 4G		X
750-8210/025-000	PFC200 G2 4ETH T	X	X
750-8212/025-000	PFC200 G2 2ETH RS T	X	X
750-8212/025-001	PFC200 G2 2ETH RS Tele T	X	X
750-8212/025-002	PFC200 G2 2ETH RS ECO Tele T	X	X
750-8212/000-100	PFC200 G2 2ETH RS BACnet/IP		X
750-8216/025-000	PFC200 G2 2ETH RS CAN DPS T	X	X
750-8216/025-001	PFC200 G2 2ETH RS CAN DPS Tele T	X	X
750-8217/025-000	PFC200 G2 2ETH RS 4G T		X
750-8210/040-000	PFC200 G2 4ETH XTR	X	X
750-8212/040-010	PFC200 G2 2ETH M12 RS XTR	X	X
750-8213/040-010	PFC200 G2 2ETH M12 CAN XTR	X	X

Important:

- 1 e!RUNTIME available for devices produced 07/2017 or later
- 2 Product discontinued, last call on 31.12.2020
- 3 **Firmware is guaranteed to be maintained until the last FW release 2021**
- 4 **New features not guaranteed for next firmware**

This firmware will be released via GitHub: <https://github.com/WAGO>

15.1 System

- [NEW] Each bridge contains its own MAC address for 2nd generation PFC200(750-821X)
- [NEW] PFC 4G: Configurable data service
- [NEW] PFC 4G: Activate SIM card with PIN/PUK
- [NEW] PFC 4G: Determine signal strength from the mobile network
- [NEW] WBM-NG: Extension by the area "Package Server"
- [NEW] WBM-NG: Password length increased to maximum 100 characters
- [NEW] WBM: Discontinuation of the legacy WBM
- [NEW] Config-tool no longer uses /etc/specific/network-interfaces.xml (do not use this file anymore - it will be removed in future versions)
- [NEW] config-tool ipdatacheck option --subnet-check is removed
- [NEW] CBM: TCP/IP settings show bridge names instead of ethernet interface labels
- [NEW] CBM: Ethernet port physical settings now support 4-port PFCs (X1, X2, X11, X12)
- [NEW] Cloud Connectivity: Add support for two parallel cloud connections
- [NEW] Cloud Connectivity: Add statically configuration of protocol version
- [NEW] Cloud Connectivity: Add support for certificate based authentication for Azure IoT Hub connections
- [NEW] Cloud Connectivity: Add option for application specific property for Azure IoT Hub connections

[FIXED]	CC-1900	Cloud Connectivity: Improve robustness of Azure IoT hub connection when using an unreliable network connection
[FIXED]	WAT31159	SEC: WBM-NG: Cookies can no longer be deleted or modified over an insecure connection
[FIXED]	WAT26409	PFC 3G: The options PREFER_GSM and PREFER_UMTS for mobile networks are no longer supported because they are not correctly considered by the modem
[FIXED]	WAT31612	PFC 3G: Visibility of the signal strength restored
[FIXED]	WAT31625	PFC 3G: Provider list for manual selection is also displayed if a SIM card without PIN is used
[FIXED]	WAT31910	Fixed restore of NTP server settings
[FIXED]	WAT31537	SEC: PPPD update
[KNOWN]	WAT31818	Under Firefox, the old WBM allowed to accept passwords of any length but only the first 32 characters were saved. In order to use these passwords in WBM-NG, only the first 32 characters of these passwords must be entered.

15.2 Runtime System

[FIXED]	WAT30312	PFC200: CODESYS2: No access after double download FW13
---------	----------	--

15.3 Fieldbus Interface & Protocols

OPC UA

[NEW]	Structures are supported
[NEW]	Security Policy Base128Rsa15 is supported
[NEW]	Activation of the Commissioning Mode
[NEW]	Change of factory settings <ul style="list-style-type: none"> • The device starts with the highest security policy (Base256Sha256). • Trust all clients is deactivated • Unlimited anonymous access is deactivated

Modbus

[FIXED]	WAT31520	ModbusSlave: Overwriting of registers / variables
---------	----------	---

The Release Note(s) and the corresponding update(s) are provided free of charge. The statutory warranty and liability regulations of §§ 521, 523 BGB apply to possible errors in the Release Note(s) or possible defects in the update (CISG is excluded). The update(s) is (are) intended to further enhance and / or to enrich our product(s), but does not mean that the previous software version was defective. In order to benefit from the improvements, we generally recommend the implementation of the update(s), but we cannot assume the final responsibility for the installation of the update(s) or their costs. Since we know neither the concrete application nor the individual conditions of use.

16 Firmware Release 03.04.10 (16)

Compatible from e!COCKPIT Version	1.7	Compatible from WAGO I/O PRO Version	2.3.9.55
Affected articles/Available for		Supported PLC	
Article Number	Designation	CDS2.3	e!Runtime
750-8100	PFC100 2ETH ECO		X
750-8101	PFC100 2ETH		X
750-8101/025-000	PFC100 2ETH T		X
750-8102	PFC100 2ETH RS		X
750-8102/025-000	PFC100 2ETH RS T		X
750-8101/000-010	PFC100 FG0 2ETH		X
750-8202	PFC200 2ETH RS ^{2,3}	X	X
750-8203	PFC200 2ETH CAN ^{2,3}	X	X
750-8204	PFC200 2ETH RS CAN ^{2,3}	X	X
750-8206	PFC200 2ETH RS CAN DPS ^{2,3}	X	X
750-8207	PFC200 2ETH RS 3G	X	X
750-8208	PFC200 2ETH RS CAN DPM	X	
750-8202/025-000	PFC200 2ETH RS T ^{2,3}	X	X
750-8202/025-001	PFC200 2ETH RS Tele T ^{2,3}	X	(X) ¹
750-8202/025-002	PFC200 2ETH RS ECO Tele T ^{2,3}	X	(X) ¹
750-8203/025-000	PFC200 2ETH CAN T ^{2,3}	X	X
750-8204/025-000	PFC200 2ETH RS CAN T ^{2,3}	X	X
750-8206/025-000	PFC200 2ETH RS CAN DPS T ^{2,3}	X	X
750-8206/025-001	PFC200 2ETH RS CAN DPS Tele T ^{2,3}	X	(X) ¹
750-8207/025-000	PFC200 2ETH RS 3G T	X	X
750-8207/025-001	PFC200 2ETH RS 3G Tele T	X	(X) ¹
750-8208/025-000	PFC200 2ETH RS CAN DPM T	X	
750-8208/025-001	PFC200 2ETH RS CAN DPM Tele T	X	
750-8202/040-000	PFC200 2ETH RS XTR	X	X
750-8202/040-001	PFC200 2ETH RS Tele XTR	X	(X) ¹
750-8206/040-000	PFC200 2ETH RS CAN DPS XTR	X	X
750-8206/040-001	PFC200 2ETH RS CAN DPS Tele XTR	X	(X) ¹
750-8202/000-011	PFC200 FG1 2ETH RS	X	X
750-8202/000-012	PFC200 FG2 2ETH RS	X	X
750-8202/000-022	PFC200 FGE 2ETH RS	X	X
750-8207/000-022	PFC200 FGE 2ETH RS 3G	X	X
750-8210	PFC200 G2 4ETH	X	X
750-8212	PFC200 G2 2ETH RS	X	X
750-8213	PFC200 G2 2ETH CAN	X	X
750-8214	PFC200 G2 2ETH RS CAN	X	X
750-8215	PFC200 G2 4ETH CAN USB		X
750-8216	PFC200 G2 2ETH RS CAN DPS	X	X

750-8217	PFC200 G2 2ETH RS 4G		X
750-8210/025-000	PFC200 G2 4ETH T	X	X
750-8212/025-000	PFC200 G2 2ETH RS T	X	X
750-8212/025-001	PFC200 G2 2ETH RS Tele T	X	X
750-8212/025-002	PFC200 G2 2ETH RS ECO Tele T	X	X
750-8212/000-100	PFC200 G2 2ETH RS BACnet/IP		X
750-8216/025-000	PFC200 G2 2ETH RS CAN DPS T	X	X
750-8216/025-001	PFC200 G2 2ETH RS CAN DPS Tele T	X	X
750-8217/025-000	PFC200 G2 2ETH RS 4G T		X
750-8210/040-000	PFC200 G2 4ETH XTR	X	X
750-8212/040-010	PFC200 G2 2ETH M12 RS XTR	X	X
750-8213/040-010	PFC200 G2 2ETH M12 CAN XTR	X	X

Important:

- 1 e!RUNTIME available for devices produced 07/2017 or later
- 2 Product discontinued, last call on 31.12.2020
- 3 Firmware is guaranteed to be maintained until the last FW release 202

This firmware will be released via GitHub: <https://github.com/WAGO>

16.1 System

- [NEW] New Web Based Management integrated. WBM has a contemporary look and feel such as an improved handling.
- [NEW] WBM-NG: network configuration adopted to support 4 ports
- [NEW] WBM-NG: configuration is based on bridges, instead of interfaces
- [NEW] WBM-NG: Improved DIP switch logic
- [NEW] SSH host keys are taken over during firmware update
- [NEW] Custom OpenVPN data is regarded during backup
- [NEW] Added curl command line tool
- [NEW] Updated tcpdump (4.9.2 -> 4.9.3)
- [NEW] Updated dropbear (2018.76 -> 2019.78)
- [NEW] Updated libcurl/curl (7.65.0 -> 7.67.0)
- [NEW] Updated net-snmp (5.7.3 -> 5.8)
- [NEW] Updated sudo (1.8.28 -> 1.8.31)
- [NEW] Updated PHP (7.3.5 -> 7.3.15)
- [NEW] Updated mdmd (0.5.3 -> 0.7.6)
- Several and improvements for configuration of internal 3G modem and additional failure diagnostics (see new version of 750-8207 manual)
- [NEW] WAT31394 Added EXT4 filesystem as SD card formatting option.
- [NEW] WAT29230 Enlargement of the CANopen master configuration memory now enables more complex CANopen project planning.
- [FIXED] WAT30870 Internal MAC address translation.
- [FIXED] WAT29930 Conflicted IP configurations.
- WAT31094

[FIXED]	WAT31179	Missing routing table update.
	WAT31114	
[FIXED]	WAT30885	Changing third DIP switch octetts is not possible.
[FIXED]	WAT30573	Modem cannot be addressed after several resets.
	WAT30910	
[FIXED]	WAT31166	Modem swichtover to GSM not possible.
[FIXED]	WAT31218	Possible loss of internal 3G modem parameter on power cycle.
[FIXED]	WAT31543	IP remains on bridge after link loss on interfaces
[FIXED]	WAT31072	Fixed CVE-2019-5134, 5135, -5155, -5156. 5157, -5166, -5167, -5168,
	WAT31071	-5169, -5170, -5171, -5172, -5173, -5174, -5175, -5176, -5177, 5178,
	WAT31068	-5179, -5180, -5181, -5182, -5185, -5186
		More information: www.wago.com/security

16.2 Fieldbus Interface & Protocols

OPC UA [NEW]

WAGO OPC UA Server available. New Server can be installed via ipk. File is available through website and support: support@wago.com

BACnet [NEW]

Add BACnet Support for PFC200 G2 (750-8212, 750-8212/025-00X, 750-8213) and Control Panel Devices (762-430X/8000-002, 762-530X/8000-002)

CAN

[FIXED]

WAT31136

Added method CAN_RX_ALL in Codesys2 CANLayer2 library. This method allows processing of CAN telegrams in order of their reception. New version of WagoCANLayer2_03.lib is required.

MQTT

[FIXED]

Fixed timestamp creation for Sparkplug NDATA messages: Use data creation time instead of transmission time

[FIXED]

Increased handshake timeout for WAGO protocol

[FIXED]

Try to reconnect automatically if MQTT broker denies connection

[KNOWN]

31190

Limit for maximum number of Trend Log (Multiple) Objects is set to 300

17 Firmware Release 03.03.11 (15)

Compatible from e!COCKPIT Version	1.6.1	Compatible from WAGO I/O PRO Version	2.3.9.55
-----------------------------------	-------	--------------------------------------	----------

Important:

(X)¹ e!RUNTIME available for devices produced 07/2017 or laterThis firmware will be released via GitHub: <https://github.com/WAGO>

17.1 System

[FIXED] WAT31102 Improved robustness by heavy ethernet traffic.

18 Firmware Release 03.03.10 (15)

Compatible from e!COCKPIT Version	1.6.1	Compatible from WAGO I/O PRO Version	2.3.9.55
-----------------------------------	-------	--------------------------------------	----------

Affected articles/Available for		Supported PLC	
Article Number	Designation	CDS2.3	e!Runtime
750-8100	PFC100 CS 2ETH ECO		X
750-8101	PFC100 CS 2ETH		X
750-8101/025-000	PFC100 CS 2ETH T		X
750-8102	PFC100 CS 2ETH RS		X
750-8102/025-000	PFC100 CS 2ETH RS T		X
750-8101/000-010	PFC100 FG0 2ETH		X
750-8202	PFC200 CS 2ETH RS	X	X
750-8203	PFC200 CS 2ETH CAN	X	X
750-8204	PFC200 CS 2ETH RS CAN	X	X
750-8206	PFC200 CS 2ETH RS CAN DPS	X	X
750-8207	PFC200 CS 2ETH RS 3G	X	X
750-8208	PFC200 CS 2ETH RS CAN DPM	X	
750-8202/025-000	PFC200 CS 2ETH RS T	X	X
750-8202/025-001	PFC200 CS 2ETH RS Tele T	X	(X) ¹
750-8202/025-002	PFC200 CS 2ETH RS ECO Tele T	X	(X) ¹
750-8203/025-000	PFC200 CS 2ETH CAN T	X	X
750-8204/025-000	PFC200 CS 2ETH RS CAN T	X	X
750-8206/025-000	PFC200 CS 2ETH RS CAN DPS T	X	X
750-8206/025-001	PFC200 CS 2ETH RS CAN DPS Tele T	X	(X) ¹
750-8207/025-000	PFC200 CS 2ETH RS 3G T	X	X
750-8207/025-001	PFC200 CS 2ETH RS 3G Tele T	X	(X) ¹
750-8208/025-000	PFC200 CS 2ETH RS CAN DPM T	X	
750-8208/025-001	PFC200 CS 2ETH RS CAN DPM Tele T	X	
750-8202/040-000	PFC200 CS 2ETH RS XTR	X	X
750-8202/040-001	PFC200 CS 2ETH RS Tele XTR	X	(X) ¹
750-8206/040-000	PFC200 CS 2ETH RS CAN DPS XTR	X	X
750-8206/040-001	PFC200 CS 2ETH RS CAN DPS Tele XTR	X	(X) ¹
750-8202/000-011	PFC200 FG1 2ETH RS	X	X
750-8202/000-012	PFC200 FG2 2ETH RS	X	X
750-8202/000-022	PFC200 FGE 2ETH RS	X	X
750-8207/000-022	PFC200 FGE 2ETH RS 3G	X	X

750-8212	PFC200 G2 2ETH RS	X	X
750-8213	PFC200 G2 2ETH CAN	X	X
750-8214	PFC200 G2 2ETH RS CAN	X	X
750-8215	PFC200 G2 4ETH CAN USB		X
750-8216	PFC200 G2 2ETH RS CAN DPS	X	X
750-8212/025-000	PFC200 G2 2ETH RS T	X	X
750-8212/025-001	PFC200 G2 2ETH RS Tele T	X	X
750-8212/025-002	PFC200 G2 2ETH RS ECO Tele T	X	X
750-8212/000-100	PFC200 G2 2ETH RS BACnet/IP		X
750-8216/025-000	PFC200 G2 2ETH RS CAN DPS T	X	X
750-8216/025-001	PFC200 G2 2ETH RS CAN DPS Tele T	X	X
750-8212/040-010	PFC200 G2 2ETH M12 RS XTR	X	X
750-8213/040-010	PFC200 G2 2ETH M12 CAN XTR	X	X

Important:

(X)¹ e!RUNTIME available for devices produced 07/2017 or later

This firmware will be released via GitHub: <https://github.com/WAGO>

18.1 System

[NEW]

The switch mode on 4-port PFC devices (750-8215) may now be configured like 2-port devices for ports X1 & X2 via WBM.

The default switch configuration on 750-8215 has changed from a fixed separated to an all switched setting.

It is now possible to configure all 4 ports, as you like via config-tool. Our next release will make this feature available via WBM.

[NEW]

By download of the CDS3 PROFINET i-Device functionality, the PROFINET-designated ports X11 & X12 are automatically combined in one bridge.

[FIXED] WAT30375

Cloud-Connectivity: Improve robustness of Azure IoT hub connection when using an unreliable network connection.

[FIXED] WAT30253

Correct impact of SMS method calls and modem status requests from Codesys IEC application to modem data service for PFC 750-8207.

18.2 Runtime System

[FIXED] WAT30561

Correct directory handling in e!Cockpit SysDirLinux library for PFC.

18.3 Fieldbus Interface & Protocols

Profibus

[FIXED] WAT28297

Correct mapping of PROFIBUS Bool variables for PFC. Possible wrong configuration of Bool arrays is now blocked in the CODESYS 2.3 PROFIBUS configurator (requires new TSP).

The Release Note(s) and the corresponding update(s) are provided free of charge. The statutory warranty and liability regulations of §§ 521, 523 BGB apply to possible errors in the Release Note(s) or possible defects in the update (CISG is excluded). The update(s) is (are) intended to further enhance and / or to enrich our product(s), but does not mean that the previous software version was defective. In order to benefit from the improvements, we generally recommend the implementation of the update(s), but we cannot assume the final responsibility for the installation of the update(s) or their costs. Since we know neither the concrete application nor the individual conditions of use.

19 Firmware Release 03.02.02 (14)

Compatible from e!COCKPIT Version	1.6	Compatible from WAGO I/O PRO Version	2.3.9.55
-----------------------------------	-----	--------------------------------------	----------

Affected articles/Available for		Supported PLC	
Article Number	Designation	CDS2.3	e!Runtime
750-8100	PFC100 CS 2ETH ECO		X
750-8101	PFC100 CS 2ETH		X
750-8101/025-000	PFC100 CS 2ETH T		X
750-8102	PFC100 CS 2ETH RS		X
750-8102/025-000	PFC100 CS 2ETH RS T		X
750-8101/000-010	PFC100 FG0 2ETH		X
750-8202	PFC200 CS 2ETH RS	X	X
750-8203	PFC200 CS 2ETH CAN	X	X
750-8204	PFC200 CS 2ETH RS CAN	X	X
750-8206	PFC200 CS 2ETH RS CAN DPS	X	X
750-8207	PFC200 CS 2ETH RS 3G	X	X
750-8208	PFC200 CS 2ETH RS CAN DPM	X	
750-8202/025-000	PFC200 CS 2ETH RS T	X	X
750-8202/025-001	PFC200 CS 2ETH RS Tele T	X	(X) ¹
750-8202/025-002	PFC200 CS 2ETH RS ECO Tele T	X	(X) ¹
750-8203/025-000	PFC200 CS 2ETH CAN T	X	X
750-8204/025-000	PFC200 CS 2ETH RS CAN T	X	X
750-8206/025-000	PFC200 CS 2ETH RS CAN DPS T	X	X
750-8206/025-001	PFC200 CS 2ETH RS CAN DPS Tele T	X	(X) ¹
750-8207/025-000	PFC200 CS 2ETH RS 3G T	X	X
750-8207/025-001	PFC200 CS 2ETH RS 3G Tele T	X	(X) ¹
750-8208/025-000	PFC200 CS 2ETH RS CAN DPM T	X	
750-8208/025-001	PFC200 CS 2ETH RS CAN DPM Tele T	X	
750-8202/040-000	PFC200 CS 2ETH RS XTR	X	X
750-8202/040-001	PFC200 CS 2ETH RS Tele XTR	X	(X) ¹
750-8206/040-000	PFC200 CS 2ETH RS CAN DPS XTR	X	X
750-8206/040-001	PFC200 CS 2ETH RS CAN DPS Tele XTR	X	(X) ¹
750-8202/000-011	PFC200 FG1 2ETH RS	X	X
750-8202/000-012	PFC200 FG2 2ETH RS	X	X

750-8202/000-022	PFC200 FGE 2ETH RS	X	X
750-8207/000-022	PFC200 FGE 2ETH RS 3G	X	X
750-8212	PFC200 G2 2ETH RS	X	X
750-8213	PFC200 G2 2ETH CAN	X	X
750-8214	PFC200 G2 2ETH RS CAN	X	X
750-8215	PFC200 G2 4ETH CAN USB		X
750-8216	PFC200 G2 2ETH RS CAN DPS	X	X
750-8212/025-000	PFC200 G2 2ETH RS T	X	X
750-8212/025-001	PFC200 G2 2ETH RS Tele T	X	X
750-8212/025-002	PFC200 G2 2ETH RS ECO Tele T	X	X
750-8212/000-100	PFC200 G2 2ETH RS BACnet/IP		X
750-8216/025-000	PFC200 G2 2ETH RS CAN DPS T	X	X
750-8216/025-001	PFC200 G2 2ETH RS CAN DPS Tele T	X	X

Important:

(X)¹ e!RUNTIME available for devices produced 07/2017 or later

This firmware will be released via GitHub: <https://github.com/WAGO>

19.1 System

[FIXED] WAT29498 e!COCKPIT BlkDrvTcp Exception
[FIXED] WAT30282 "force" on the Software Uploads page in the Web based Management does not work

19.2 Runtime System

[NEW] e!RUNTIME Upgrade to Version 3.5.14.3

19.3 Fieldbus Interface & Protocols

Cloud Connectivity

[NEW] Compression method integrated
[NEW] WAGO protocol extended by data type String
[NEW] Recovery of an application backup via WAGO Cloud (application update)
[NEW] Restoring an application backup via WAGO Cloud in the context of a firm-ware update (device update)

OPC UA

[FIXED] WAT29993 OPC UA inactive after firewall activation.

Profibus

[FIXED] WAT30087 e!COCKPIT: Profibus Slave: wrong input data when mapping to existing variables
[FIXED] WAT30170 Profibus slave: no correct data transmission of array slots when accessing via addresses / existing variables

19.4 Libraries

[FIXED] WAT30132 WagoSysCurl does not consider the udiStringLength of the method curl_easy_setopt_STRING2

20 Firmware Release 03.01.07 (13)

Compatible from e!COCKPIT Version	1.5.1	Compatible from WAGO I/O PRO Version	2.3.9.55
-----------------------------------	-------	--------------------------------------	----------

Affected articles/Available for		Supported PLC	
Article Number	Designation	CDS2.3	e!Runtime
750-8100	PFC100 CS 2ETH ECO		X
750-8101	PFC100 CS 2ETH		X
750-8101/025-000	PFC100 CS 2ETH T		X
750-8102	PFC100 CS 2ETH RS		X
750-8102/025-000	PFC100 CS 2ETH RS T		X
750-8101/000-010	PFC100 FG0 2ETH		X
750-8202	PFC200 CS 2ETH RS	X	X
750-8203	PFC200 CS 2ETH CAN	X	X
750-8204	PFC200 CS 2ETH RS CAN	X	X
750-8206	PFC200 CS 2ETH RS CAN DPS	X	X
750-8207	PFC200 CS 2ETH RS 3G	X	X
750-8208	PFC200 CS 2ETH RS CAN DPM	X	
750-8202/025-000	PFC200 CS 2ETH RS T	X	X
750-8202/025-001	PFC200 CS 2ETH RS Tele T	X	(X) ¹
750-8202/025-002	PFC200 CS 2ETH RS ECO Tele T	X	(X) ¹
750-8203/025-000	PFC200 CS 2ETH CAN T	X	X
750-8204/025-000	PFC200 CS 2ETH RS CAN T	X	X
750-8206/025-000	PFC200 CS 2ETH RS CAN DPS T	X	X
750-8206/025-001	PFC200 CS 2ETH RS CAN DPS Tele T	X	(X)¹
750-8207/025-000	PFC200 CS 2ETH RS 3G T	X	X
750-8207/025-001	PFC200 CS 2ETH RS 3G Tele T	X	(X) ¹
750-8208/025-000	PFC200 CS 2ETH RS CAN DPM T	X	
750-8208/025-001	PFC200 CS 2ETH RS CAN DPM Tele T	X	
750-8202/040-000	PFC200 CS 2ETH RS XTR	X	X
750-8202/040-001	PFC200 CS 2ETH RS Tele XTR	X	X
750-8206/040-000	PFC200 CS 2ETH RS CAN DPS XTR	X	X
750-8206/040-001	PFC200 CS 2ETH RS CAN DPS Tele XTR	X	X
750-8202/000-011	PFC200 FG1 2ETH RS	X	X
750-8202/000-012	PFC200 FG2 2ETH RS	X	X
750-8202/000-022	PFC200 FGE 2ETH RS	X	X
750-8207/000-022	PFC200 FGE 2ETH RS 3G	X	X
750-8212	PFC200 G2 2ETH RS	X	X
750-8213	PFC200 G2 2ETH CAN	X	X
750-8214	PFC200 G2 2ETH RS CAN	X	X
750-8215	PFC200 G2 4ETH CAN USB		X
750-8216	PFC200 G2 2ETH RS CAN DPS	X	X
750-8212/025-000	PFC200 G2 2ETH RS T	X	X
750-8212/025-001	PFC200 G2 2ETH RS Tele T	X	X
750-8212/025-002	PFC200 G2 2ETH RS ECO Tele T	X	X
750-8212/000-100	PFC200 G2 2ETH RS BACnet/IP		X
750-8216/025-000	PFC200 G2 2ETH RS CAN DPS T	X	X
750-8216/025-001	PFC200 G2 2ETH RS CAN DPS Tele T	X	X

Important:(X)¹ e!RUNTIME available for devices produced 07/2017 or laterThis firmware will be released via GitHub: <https://github.com/WAGO>**Firmware 03.01.07 (13) is not permitted to be used for Profibus Slave Devices. (750-8206, 750-8216, and variants; see above)****20.1 System**

[NEW]	New Device: PFC200 with BACnet (750-8212/000-100)
[NEW]	Backups can be encrypted via password.
[NEW]	PHP updated to 7.3
[NEW]	OpenSSL updated to 1.0.2q
[NEW]	OpenSSH updated to 7.9p1
[NEW]	OpenVPN updated to 2.4.6
[NEW]	CA certificated updated to 2019.02.11
[NEW]	CURL updated to 7.65
[NEW]	lighttpd updated to 1.4.53

20.2 Runtime System

[FIXED]	WAT26804	CODESYS 2.3: No access after double download.
---------	----------	---

20.3 Fieldbus Interface & Protocols**20.3.1 BACnet**

[NEW]	Integration of BACnet profile B-BC (can only be used with 750-8212/000-100)
[NEW]	Firmware version 13 is officially listed at BACnet International with the BTL mark.

Cloud Connectivity

[NEW]	WebSockets are supported for the WAGO protocol.
-------	---

20.4 Libraries

[FIXED]	WAT29373	WagoAppHttp: Data sporadically in header.
[FIXED]	WAT29513	WagoAppFTP: FTP/FTPS client freezes during processing.

21 Firmware Release 03.00.39 (12)

Compatible from e!COCKPIT Version	1.5	Compatible from WAGO I/O PRO Version	2.3.9.55
-----------------------------------	-----	--------------------------------------	----------

This firmware will be released via GitHub: <https://github.com/WAGO>**21.1 System**

[FIXED]	WAT28151 WAT28953 WAT28822 WAT28853	Unreliable behavior of the mobile connection (750-8207)
---------	--	---

[FIXED]	WAT29247	Directory structure of /home folder was destroyed after system backup
[NEW]	WAT29453	Checksum of CODESYS 2.3 project is shown in WBM
[NEW]	WAT29454	Advanced Intrusion Detection Environment (AIDE) can be used to identify changes of filesystem

21.2 Operating System

[NEW]	Kernel Update to version 4.9.146
-------	----------------------------------

21.3 Fieldbus Interface & Protocols

Cloud Connectivity

[NEW]	Support of SAP Cloud
[NEW]	Azure SDK uses websockets
[NEW]	Retain-parameter visible in WBM
[NEW]	Backup / Restore extended by parameter migration

Profibus

[FIXED]	WAT29313 WAT28790	Using Bool and Real variables under Profibus does not work properly.
---------	----------------------	--

22 Firmware Release 03.00.35 (12)

Compatible from e!COCKPIT Version	1.5	Compatible from WAGO I/O PRO Version	2.3.9.55
-----------------------------------	-----	--------------------------------------	----------

Affected articles/Available for		Supported PLC	
Article Number	Designation	CDS2.3	e!Runtime
750-8100	PFC100 CS 2ETH ECO		X
750-8101	PFC100 CS 2ETH		X
750-8101/025-000	PFC100 CS 2ETH T		X
750-8102	PFC100 CS 2ETH RS		X
750-8102/025-000	PFC100 CS 2ETH RS T		X
750-8101/000-010	PFC100 FG0 2ETH		X
750-8202	PFC200 CS 2ETH RS	X	X
750-8203	PFC200 CS 2ETH CAN	X	X
750-8204	PFC200 CS 2ETH RS CAN	X	X
750-8206	PFC200 CS 2ETH RS CAN DPS	X	X
750-8207	PFC200 CS 2ETH RS 3G	X	X
750-8208	PFC200 CS 2ETH RS CAN DPM	X	
750-8202/025-000	PFC200 CS 2ETH RS T	X	X
750-8202/025-001	PFC200 CS 2ETH RS Tele T	X	(X) ¹
750-8202/025-002	PFC200 CS 2ETH RS ECO Tele T	X	(X) ¹
750-8203/025-000	PFC200 CS 2ETH CAN T	X	X
750-8204/025-000	PFC200 CS 2ETH RS CAN T	X	X
750-8206/025-000	PFC200 CS 2ETH RS CAN DPS T	X	X
750-8206/025-001	PFC200 CS 2ETH RS CAN DPS Tele T	X	(X) ¹
750-8207/025-000	PFC200 CS 2ETH RS 3G T	X	X
750-8207/025-001	PFC200 CS 2ETH RS 3G Tele T	X	(X) ¹
750-8208/025-000	PFC200 CS 2ETH RS CAN DPM T	X	
750-8208/025-001	PFC200 CS 2ETH RS CAN DPM Tele T	X	
750-8202/040-000	PFC200 CS 2ETH RS XTR	X	X
750-8202/040-001	PFC200 CS 2ETH RS Tele XTR	X	(X) ¹
750-8206/040-000	PFC200 CS 2ETH RS CAN DPS XTR	X	X
750-8206/040-001	PFC200 CS 2ETH RS CAN DPS Tele XTR	X	(X) ¹
750-8202/000-011	PFC200 FG1 2ETH RS	X	X
750-8202/000-012	PFC200 FG2 2ETH RS	X	X
750-8202/000-022	PFC200 FGE 2ETH RS	X	X
750-8207/000-022	PFC200 FGE 2ETH RS 3G	X	X
750-8212	PFC200 G2 2ETH RS	X	X
750-8213	PFC200 G2 2ETH CAN	X	X
750-8214	PFC200 G2 2ETH RS CAN	X	X
750-8215	PFC200 G2 4ETH CAN USB		X
750-8216	PFC200 G2 2ETH RS CAN DPS	X	X
750-8212/025-000	PFC200 G2 2ETH RS T	X	X
750-8212/025-001	PFC200 G2 2ETH RS Tele T	X	X
750-8212/025-002	PFC200 G2 2ETH RS ECO Tele T	X	X
750-8216/025-000	PFC200 G2 2ETH RS CAN DPS T	X	X
750-8216/025-001	PFC200 G2 2ETH RS CAN DPS Tele T	X	X

Important:

(X)¹ e!RUNTIME available for devices produced 07/2017 or later

This firmware will be released via GitHub: <https://github.com/WAGO>

22.1 System

[FIXED]	WAT29498	Net-LED shows wrong connection state
[FIXED]	WAT25828	Restricted remote connectivity between e!Cockpit and 750-8207 via 3G modem and VPN
[FIXED]	WAT26533	WebVisu may open too many sockets
[FIXED]	WAT27038	/va/log/access.log may grow up to 4 MBytes
[KNOWN]	WAT27110	SNMP exceptions while sending Messages from different Tasks
[KNOWN]	WAT27216	Ethernet Broadcast and Bandwidth limitation does not work properly.

22.2 Runtime System

[NEW]		e!RUNTIME Upgrade to Version 3.5.13.2
[FIXED]	WAT27447	Download of e!Runtime project may fail, if WagoSysKbusTerminalControl is used
[FIXED]	WAT27748	e!Runtime may crash, when SD card is plugged or removed

22.3 Operating System

[NEW]		Integraton of kernel features for Docker (Docker Ready)
[NEW]		Compiler Update to Linaro GCC 5.5
[NEW]		ptxdist-Update to Version 2017.11.1
[FIXED]	WAT26710	Access of SD card may procude kernel log entries
[KNOWN]	WAT21386	Pointer operation in retain memory with wrong alignment forces execution

22.4 Fieldbus Interface & Protocols

EtherCAT		
[NEW]		Integration of EtherCAT Master (can only be used with license)
Cloud Connectivity		
[NEW]		Handshake between WAGO Cloud and PFCx00 (Cloud Connectivity)
[NEW]		Event-based publishing of data via the Wago protocol
[NEW]		Integration of native MQTT
[NEW]		Support of Sparkplug protocol (can only be used with license)
OPC UA		
[FIXED]	WAT23100	OPC UA low update rate in case of more than 1000 variables
Profibus		
[KNOWN]	WAT29313	Using BOOL variables under Profibus does not work properly.

22.5 Libraries

[NEW]		SQLite Databas Management System (including IEC Library)
[KNOWN]	WAT26085	WagoAppProcessorLoad returns invalid cpu load value, calculation includes not all system processes
[KNOWN]	WAT27060	WagoConfigToolLIB.lib cannot read some networking settings when configured with DHCP

23 Firmware Release 02.08.35 (11)

23.1 System

[FIXED]	WAT24029, WAT24097	Controller stops working after an indefinite period of time.
[KNOWN]	WAT26968	ADI DAL mode "Unconfigured" does not work. Only C/C++ programmers are affected.

23.2 Runtime System

[FIXED]	WAT26608	SymARTI communication does not work without login
[FIXED]	WAT26483	"Online Change" download may result in a short flickering of the outputs.
[FIXED]	WAT25908	e!Runtime: Modbus TCP master does not send request if slave was not available during start up.
[NEW]	WAT	e!Runtime: WagoSysSSL, connection to the original OpenSSL library

23.3 Fieldbus Interface & Protocols

23.3.1 Cloud Connectivity

[FIXED]	WAT26510	Loss of data during offline logging.
[FIXED]	WAT26870	High memory usage on bad radio conditions

23.4 Libraries

[FIXED]	WAT26587	WagoLibNetSNMP: Register of custom IDs does not work
[FIXED]	WAT24127	WagoLibNetSNMP: Excessive settings of OIDs could cause connection aborts in debug mode.

24 Firmware Release 02.08.31 (11)

24.1 System

[FIXED]	WAT25630	SMTP is not supported.
[FIXED]	WAT24264	Bandwidth and broadcast limitation does not work.
[FIXED]	WAT26118	750-8207: Memory leak in the modem daemon.

24.2 Fieldbus Interface & Protocols

[FIXED]	WAT25792	NMT-Master doesn't start the slaves correctly after "Bus Off".
[FIXED]	WAT25815	Slave does not work properly when Runtime is in Stop.
[FIXED]	WAT24216	High jitter of the sync telegram.
[FIXED]	WAT25418	CAN task stops after some time.
[FIXED]	WAT25204	CAN transmission error when using Heartbeat.

OPC-UA

[FIXED]	WAT25214	Object "Service Level" is set to "0". (now "200")
---------	----------	---

25 Firmware Release 02.08.26 (11)

25.1 System

[FIX] WAT25608 PFC100: Controller cannot read the DIP Switch settings.

26 Firmware Release 02.08.25 (11)

Affected articles/Available for		Supported PLC	
Article Number	Designation	CDS2.3	e!Runtime
750-8100	PFC100 CS 2ETH ECO		X
750-8101	PFC100 CS 2ETH		X
750-8101/025-000	PFC100 CS 2ETH T		X
750-8102	PFC100 CS 2ETH RS		X
750-8102/025-000	PFC100 CS 2ETH RS T		X
750-8101/000-010	PFC100 FG0 2ETH		X
750-8202	PFC200 CS 2ETH RS	X	X
750-8203	PFC200 CS 2ETH CAN	X	X
750-8204	PFC200 CS 2ETH RS CAN	X	X
750-8206	PFC200 CS 2ETH RS CAN DPS	X	X
750-8207	PFC200 CS 2ETH RS 3G	X	X
750-8208	PFC200 CS 2ETH RS CAN DPM	X	
750-8202/025-000	PFC200 CS 2ETH RS T	X	X
750-8202/025-001	PFC200 CS 2ETH RS Tele T	X	(X) ¹
750-8202/025-002	PFC200 CS 2ETH RS ECO Tele T	X	(X) ¹
750-8203/025-000	PFC200 CS 2ETH CAN T	X	X
750-8204/025-000	PFC200 CS 2ETH RS CAN T	X	X
750-8206/025-000	PFC200 CS 2ETH RS CAN DPS T	X	X
750-8206/025-001	PFC200 CS 2ETH RS CAN DPS Tele T	X	(X) ¹
750-8207/025-000	PFC200 CS 2ETH RS 3G T	X	X
750-8207/025-001	PFC200 CS 2ETH RS 3G Tele T	X	(X) ¹
750-8208/025-000	PFC200 CS 2ETH RS CAN DPM T	X	
750-8208/025-001	PFC200 CS 2ETH RS CAN DPM Tele T	X	
750-8202/040-000	PFC200 CS 2ETH RS XTR	X	X
750-8202/040-001	PFC200 CS 2ETH RS Tele XTR	X	(X) ¹
750-8206/040-000	PFC200 CS 2ETH RS CAN DPS XTR	X	X
750-8206/040-001	PFC200 CS 2ETH RS CAN DPS Tele XTR	X	(X) ¹
750-8202/000-011	PFC200 FG1 2ETH RS	X	X
750-8202/000-012	PFC200 FG2 2ETH RS	X	X
750-8202/000-022	PFC200 FGE 2ETH RS	X	X
750-8207/000-022	PFC200 FGE 2ETH RS 3G	X	X
750-8212	PFC200 G2 2ETH RS	X	X
750-8213	PFC200 G2 2ETH CAN	X	X
750-8214	PFC200 G2 2ETH RS CAN	X	X
750-8216	PFC200 G2 2ETH RS CAN DPS	X	X
750-8212/025-000	PFC200 G2 2ETH RS T	X	X

750-8212/025-001	PFC200 G2 2ETH RS Tele T	X	X
750-8212/025-002	PFC200 G2 2ETH RS ECO Tele T	X	X
750-8216/025-000	PFC200 G2 2ETH RS CAN DPS T	X	X
750-8216/025-001	PFC200 G2 2ETH RS CAN DPS Tele T	X	X

Important:

(X)¹ In this version the Telecontrol feature is not available in e!RUNTIME.

26.1 System

[NEW]	WAT	MQTT support is part of the standard firmware package
[FIXED]	WAT22634	Memory leak in the mdmd
[FIXED]	WAT24268	GSM-Modem reports "Error while Reading SIM-Data" when automatic switch from UMTS to GSM is performed
[FIXED]	WAT23086	Controller may crash while scanning with e!COCKPIT
[FIXED]	WAT21999	Memory leak in the LED server daemon
[FIXED]	WAT	Several security leaks, see also WAGO homepage for further details on known security vulnerabilities
[KNOWN]	WAT25270	The LED stops blinking after long term at times
[KNOWN]	WAT24264	Ethernet broadcast and bandwidth limitation does not work properly
[KNOWN]	WAT25246	IPsec implementation is not conform according to the RFC
[KNOWN]	WAT22573	SNMP exceptions while sending messages from different tasks
[KNOWN]	WAT22155	Installation of IPK packages may fail because of timeouts

26.2 Runtime System

[NEW]	WAT	CODESYS 3.5 SP11 Patch 1
[FIXED]	WAT24228	The "plclinux_rt" service accepts different unauthenticated actions. For further information see Wago homepage Security
[FIXED]	WAT25401	If port authentication of CODESYS 2.3 is activated, OPC communication is not possible if you are logged in at the same time as the CODESYS 2.3 GUI. Furthermore, only the login from an OPC server is possible at the same time.
[FIXED]	WAT22955	e!RUNTIME: MODBUS RTU Master does not communicate with all Slaves
[KNOWN]	WAT25161	The Runtime is terminated by SNMP GET call if the OID value is greater than 40 characters
[KNOWN]	WAT25006	Character loss on onboard RS485 with e! RUNTIME at 115200 Baud and 57600 Baud
[KNOWN]	WAT24697	Boot project will be deleted at runtime startup if inconsistency is detected
[KNOWN]	WAT24346	e!RUNTIME Crash when combining forced variables, single cycle, complex terminals and online change
[KNOWN]	WAT25099	e!RUNTIME: For projects with modules according to the list (WAT25099_ModuleList.docx) rest cold and warm causes a crash.
[KNOWN]	WAT24326	With CODESYS V2.3, the SNMP_GET function no longer works after online change

26.3 Web Based Management

[NEW]	WAT	Configuration for router / NAT / IP masquerading
[KNOWN]	WAT25527	Incorrect access rights for routing page

26.4 Operating System

[NEW]	WAT	Linux Kernel Version 4.9.47-rt37
-------	-----	----------------------------------

26.5 Fieldbus Interface & Protocols

Modbus		
[NEW]	WAT	Improvement of Diagnosis : TCP connection status, errors, error reactions (Hold Last Value/Set to Zero)
[FIXED]	WAT22571	The Modbus process image is not consistent in itself when using ARRAY.
[KNOWN]	WAT22592	Controller may crash while using BOOL as RETAIN via MODBUS Configurator
CAN/CANopen		
[FIXED]	WAT25204	CAN transmission error when using Heartbeat telegrams
[KNOWN]	WAT24358	CANopen Baudrate 800 kB not supported on new controllers 750-821x
Profibus		
[FIXED]	WAT23591	PROFIBUS: timing problems with 12 MBaud
[FIXED]	WAT23828	750-8206 PROFIBUS Slave Array of Bool Mapping Master Slave not complete
[KNOWN]	WAT25074	750-8208: Problems with recalculation of PROFIBUS addresses while adding new modules inside PROFIBUS Master configurator
[KNOWN]	WAT25529	750-8208: A Project download fails if profibus I/O data size is greater than 3528 byte. (The documented I/O data size of the Profibus master is reduced in this firmware)
[KNOWN]	WAT25517	The use of BusDiag.lib is limited to older hardware according to buffer size limitation. Strictly recommended is the use of the wago library WAGO_BusDiag_01.lib.
OPC UA (3S runtime component)		
[KNOWN]	WAT25214	OPC UA Object "Service Level" default value is 0
[KNOWN]	WAT23100	OPC UA low update rate in case of more than 1000 variables
[KNOWN]	WAT22546	OPC UA: Wrong note IDs when handling with 2D Arrays

26.6 Libraries

[FIXED]	WAT	WagoLibModbus_IP_01.lib: MODBUS does not reconnect after connection error
[FIXED]	WAT21649	CODESYS 2.3: K-Bus does not synchronize when used with sercom.lib or WagoLibKBus.lib
[KNOWN]	WAT22438	WagoConfigToolLIB.lib cannot read some networking settings when configured with DHCP

27 Firmware Release 02.07.07 (10)

Affected articles/Available for		Supported PLC	
Article Number	Designation	CDS2.3	e!Runtime
750-8100	PFC100 CS 2ETH ECO		X
750-8101	PFC100 CS 2ETH		X
750-8101/025-000	PFC100 CS 2ETH T		X
750-8102	PFC100 CS 2ETH RS		X
750-8102/025-000	PFC100 CS 2ETH RS T		X
750-8202	PFC200 CS 2ETH RS	X	X

750-8203	PFC200 CS 2ETH CAN	X	X
750-8204	PFC200 CS 2ETH RS CAN	X	X
750-8206	PFC200 CS 2ETH RS CAN DPS	X	X
750-8207	PFC200 CS 2ETH RS 3G	X	X
750-8208	PFC200 CS 2ETH RS CAN DPM	X	
750-8202/025-000	PFC200 CS 2ETH RS T	X	X
750-8202/025-001	PFC200 CS 2ETH RS Tele T	X	
750-8202/025-002	PFC200 CS 2ETH RS ECO Tele T	X	
750-8203/025-000	PFC200 CS 2ETH CAN T	X	X
750-8204/025-000	PFC200 CS 2ETH RS CAN T	X	X
750-8206/025-000	PFC200 CS 2ETH RS CAN DPS T	X	X
750-8206/025-001	PFC200 CS 2ETH RS CAN DPS Tele T	X	
750-8207/025-000	PFC200 CS 2ETH RS 3G T	X	X
750-8207/025-001	PFC200 CS 2ETH RS 3G Tele T	X	
750-8208/025-000	PFC200 CS 2ETH RS CAN DPM T	X	
750-8202/040-000	PFC200 CS 2ETH RS XTR	X	X
750-8202/040-001	PFC200 CS 2ETH RS Tele XTR	X	
750-8206/040-000	PFC200 CS 2ETH RS CAN DPS XTR	X	X
750-8206/040-001	PFC200 CS 2ETH RS CAN DPS Tele XTR	X	
750-8202/000-012	PFC200 FG2 2ETH RS	X	X
750-8202/000-022	PFC200 FGE 2ETH RS	X	X

27.1 System

- [FIXED] WAT22022 Sometimes NTP settings were overwritten after reboot.
 [FIXED] WAT23465 Permanent debugging with IO-Check or e!COCKPIT over several days could result into a system crash.

27.2 Runtime System

- [FIXED] WAT23029 Security Advisory (ICSA-17-087-02)
 CoDeSys V2.3 Webserver updated to V1.1.9.18

27.3 Web Based Management

None

27.4 Operating System

None

27.5 Fieldbus Interface & Protocols

Modbus

- [FIXED] WAT22571 Modbus process data consistency was not ensured for larger arrays

CAN/CANopen

[FIXED]	WAT22728	Error message "PDO-Mapping 1601-1 Failed" after download of an e!Cockpit project
[FIXED]	WAT21010	Library CIA405_NMT showed a wrong error message "0x25" for a non-existing device
[FIXED]	WAT20942	Bus OFF LED was switching back to green also if there is no physical connection
[FIXED]	WAT20890	Function block CANOPEN_DIAG showed STATE UNKNOWN if a device(node guarding) was stopped

Profibus

None

OPC UA (3S runtime component)

None

27.6 Libraries

[NEW]	-/-	WagoAppSMI – Library for SMI modules 753-1630/-1631
[FIXED]	WAT22189	WagoSysCurl now support up to 1023 characters

28 Firmware Release 02.06.20 (09)

Affected articles/Available for		Supported PLC	
Article Number	Designation	CDS2.3	e!Runtime
750-8100	PFC100 CS 2ETH ECO		X
750-8101	PFC100 CS 2ETH		X
750-8101/025-000	PFC100 CS 2ETH T		X
750-8102	PFC100 CS 2ETH RS		X
750-8102/025-000	PFC100 CS 2ETH RS T		X
750-8202	PFC200 CS 2ETH RS	X	X
750-8203	PFC200 CS 2ETH CAN	X	X
750-8204	PFC200 CS 2ETH RS CAN	X	X
750-8206	PFC200 CS 2ETH RS CAN DPS	X	X
750-8207	PFC200 CS 2ETH RS 3G	X	X
750-8208	PFC200 CS 2ETH RS CAN DPM	X	
750-8202/025-000	PFC200 CS 2ETH RS T	X	X
750-8202/025-001	PFC200 CS 2ETH RS Tele T	X	
750-8202/025-002	PFC200 CS 2ETH RS ECO Tele T	X	
750-8203/025-000	PFC200 CS 2ETH CAN T	X	X
750-8204/025-000	PFC200 CS 2ETH RS CAN T	X	X
750-8206/025-000	PFC200 CS 2ETH RS CAN DPS T	X	X

750-8206/025-001	PFC200 CS 2ETH RS CAN DPS Tele T	X	
750-8207/025-000	PFC200 CS 2ETH RS 3G T	X	X
750-8207/025-001	PFC200 CS 2ETH RS 3G Tele T	X	
750-8208/025-000	PFC200 CS 2ETH RS CAN DPM T	X	
750-8202/040-000	PFC200 CS 2ETH RS XTR	X	X
750-8202/040-001	PFC200 CS 2ETH RS Tele XTR	X	
750-8206/040-000	PFC200 CS 2ETH RS CAN DPS XTR	X	X
750-8206/040-001	PFC200 CS 2ETH RS CAN DPS Tele XTR	X	
750-8202/000-012	PFC200 FG2 2ETH RS	X	X
750-8202/000-022	PFC200 FGE 2ETH RS	X	X

28.1 System

[FIXED]	WAT22713	Tcpdump Packages updated to 4.9.0
[FIXED]	WAT22505	OpenVPN – After time x no communication possible despite established connection
[FIXED]	WAT22021	PFC200 loses NTP client settings
[FIXED]	WAT22219	Failure to execute the PING via FBPing can result in connection problems via Ethernet
[FIXED]	WAT22158	Insecure encryption algorithms in FTPS server
[FIXED]	WAT22021	PFC200 loses NTP client settings
[FIXED]	WAT21503	The firewall does not allow the IEC60870-5-104 and IEC61850 protocols
[FIXED]	WAT21487	Malfunction with RS485 and parity none on onboard serial interface
[FIXED]	WAT21457	Syslog server accessible from outside
[FIXED]	WAT21407	Various security problems in the configtools scripts
[FIXED]	WAT21313	PFC100 : Inaccuracy of the real-time clock
[FIXED]	WAT20915	PFC100: Data corruption when reading the retentive data
[FIXED]	WAT16121	PHP Version is sent inside HTTP header
[FIXED]	WAT15970	Reflected cross site scripting
[FIXED]	WAT21999	The LED server daemon has a memory leak.
[NEW]	WAT21777	Libcurl updated to version 7.51.0
[NEW]	-/-	OpenVPN updated to version 2.3.7
[NEW]	WAT21966	IPsec Strongswan updated to version 5.3.5
[NEW]	-/-	Firewall iptables updated to version 1.4.16.3
[NEW]	-/-	SSH Server dropbear updated to version 2016.74
[NEW]	WAT21774	SFTP client function makes it possible to exchange files with devices in the delivery state
[NEW]	WAT21391	750-8207: Read IMEI by WBM and Ethernet-Settings
[NEW]	-/-	PHP server updated to version 5.6.27
[NEW]	-/-	Older insecure encryption algorithms are removed
[NEW]	-/-	TLS 1.2 support implemented
[NEW]	-/-	SCEP (Simple Certificate Enrollment Protocol) client implemented
[NEW]	-/-	Auto log off when the console is inactive
[KNOWN]	-/-	MySQL is not compatible with PHP server version 5.6.27 update

28.2 Runtime System

[FIXED]	WAT22214	Improved performance in combination with complex modules
[FIXED]	WAT21806	DoS attack on CoDeSys V2 through freely available Python scripts
[NEW]	-/-	e!RUNTIME: CODESYS runtime updated to version 3.5.9.1
[NEW]	WAT21478	Default value changed with KBus startup behavior (configured/actual comparison)
[NEW]	WAT19293	Number of PLC-Handler connections increased to 16 (old = 4)

28.3 Web Based Management

[FIXED]	WAT21973	Security documentation about TLS configuration inaccurate
[NEW]		Auto log off when the WBM is inactive

28.4 Operating System

[KNOWN]	WAT22712	Cannot update software via Package Manager while firewall is activated
[KNOWN]	WAT17785	Update from FW04: The controller has to be restarted once by PowerOff/On after the successful firmware update and to verify that the firmware update has been successful

28.5 Fieldbus Interface & Protocols

Modbus		
[KNOWN]	WAT22571	The Modbus process image in is not consistent with use of data type ARRAY
CAN/CANopen		
[FIXED]	WAT20635	The PFC200 as a CANopen master sends reset node to all nodes after a break.
Profibus		
		None
OPC UA (3S runtime component)		
[FIXED]	CDS-46860	OPCUA Server: Compliance test fails for Linux / PPC because browsing is impossible
[FIXED]	CDS-46188	OPC UA Server: on slow ARM devices, error messages appear in logger
[FIXED]	CDS-46049	OPC UA Server: no data refresh after reset of the PLC
[FIXED]	CDS-39725	SymbolConfiguration: Allow configuration of export of comments for OPC/UA
[FIXED]	WAT22171	OPC UA server cannot be disabled
[FIXED]	WAT20332	OPC UA Cannot be connected from Xenon OPC-Client

28.6 Libraries

[FIXED]	WAT22595	WagoLibSSL: SSL_CTX_set_method does not work
[NEW]	-/-	Ethernet/IPAdapter Library implemented
[NEW]	-/-	WagoLibFTP with SFTP support implemented
[KNOWN]	WAT22595	By updating the OpenSSL with the CoDeSys V2.3 library WagoLibSSL it is no longer possible to use the methods of the SSLv2. Instead, use SSLv23 or higher. The default is TLS V1.2

29 Firmware Release 02.05.23 (08)

Affected articles/Available for		Supported PLC	
Article Number	Designation	CDS2.3	e!Runtime
750-8100	PFC100 CS 2ETH ECO		X
750-8101	PFC100 CS 2ETH		X
750-8101/025-000	PFC100 CS 2ETH T		X
750-8102	PFC100 CS 2ETH RS		X
750-8102/025-000	PFC100 CS 2ETH RS T		X
750-8202	PFC200 CS 2ETH RS	X	X
750-8203	PFC200 CS 2ETH CAN	X	X
750-8204	PFC200 CS 2ETH RS CAN	X	X
750-8206	PFC200 CS 2ETH RS CAN DPS	X	X
750-8207	PFC200 CS 2ETH RS 3G	X	X
750-8202/025-000	PFC200 CS 2ETH RS T	X	X
750-8202/025-001	PFC200 CS 2ETH RS Tele T	X	
750-8202/025-002	PFC200 CS 2ETH RS ECO Tele T	X	
750-8203/025-000	PFC200 CS 2ETH CAN T	X	X
750-8204/025-000	PFC200 CS 2ETH RS CAN T	X	X
750-8206/025-000	PFC200 CS 2ETH RS CAN DPS T	X	X
750-8206/025-001	PFC200 CS 2ETH RS CAN DPS Tele T	X	
750-8207/025-000	PFC200 CS 2ETH RS 3G T	X	X
750-8207/025-001	PFC200 CS 2ETH RS 3G Tele T	X	
750-8202/040-000	PFC200 CS 2ETH RS XTR	X	X
750-8202/040-001	PFC200 CS 2ETH RS Tele XTR	X	
750-8206/040-000	PFC200 CS 2ETH RS CAN DPS XTR	X	X
750-8206/040-001	PFC200 CS 2ETH RS CAN DPS Tele XTR	X	

29.1 System

[FIXED]	WAT20045	Tool "Ethernet Settings" failed to finish the write command
[FIXED]	WAT19844	750-8207: Signal strength LED didn't work
[FIXED]	WAT18914	Mounting the SD card after pull out/in during file access
[NEW]	WAT18216	IO-Check: Setting of module parameters
[FIXED]	WAT18494	Not accessible caused by alternating the switch mode to separated
[NEW]	WAT16609	Firewall user filter allow white and black listing
[FIXED]	WAT15953	Firewall VPN interface not selectable

[NEW]	WAT14096	New error code for number of modules to high (1 + 16)
[NEW]	WAT13149	Dedicated routes for the two gateways

29.2 Runtime System

[NEW]		e!RUNTIME: New CODESYS runtime version 3.5.8.1
[FIXED]	WAT20915	PFC100: Data corruption when reading the retentive data
[FIXED]	WAT18339	Short local bus interruption caused by SNMP queries
[FIXED]	WAT17256	Self-made SNMP OIDs accepted not initialized TLV parameter
[New]	WAT12500	TCM mode for configuration of the 750-647 in run mode
[FIXED]	WAT10903	SysFileDelete ignore write protection

29.3 Web Based Management

None

29.4 Operating System

[FIXED]	WAT15975	Warning "In-band Error seen by USB_OTG at address0"
---------	----------	---

29.5 Fieldbus Interface & Protocols

Modbus

[NEW]		Alternative watchdog as with the 750-88X implemented
-------	--	--

CAN/CANopen

[NEW]	WAT16803	Supports CANopen device profile DS405
-------	----------	---------------------------------------

Profibus

None

29.6 Libraries

[FIXED]	WAT20227	Sercom.lib: ACCESS VIOLATION if used COM port number >=2
[FIXED]	WAT20022	e!Runtime WagoAppSocket: FbUdpPcketClient didn't reset the trigger input
[FIXED]	WAT19383	e!Runtime WagoSysFileDir: Folder creation on a not existing media caused system crash
[FIXED]	WAT18322	e!Runtime WagoAppTime: Caused segmentation faults

30 Firmware Release 02.04.24 (07)

Not released.

31 Firmware Release 02.04.22 (06)

Affected articles/Available for	
Article Number	Designation
750-8100	PFC100 CS 2ETH ECO
750-8101	PFC100 CS 2ETH
750-8102	PFC100 CS 2ETH RS
750-8202	PFC200 CS 2ETH RS
750-8203	PFC200 CS 2ETH CAN
750-8204	PFC200 CS 2ETH RS CAN
750-8206	PFC200 CS 2ETH RS CAN DPS
750-8207	PFC200 CS 2ETH RS 3G
750-8202/025-000	PFC200 CS 2ETH RS T
750-8202/025-001	PFC200 CS 2ETH RS Tele T
750-8202/025-002	PFC200 CS 2ETH RS ECO Tele T
750-8203/025-000	PFC200 CS 2ETH CAN T
750-8204/025-000	PFC200 CS 2ETH RS CAN T
750-8206/025-000	PFC200 CS 2ETH RS CAN DPS T
750-8206/025-001	PFC200 CS 2ETH RS CAN DPS Tele T
750-8207/025-000	PFC200 CS 2ETH RS 3G T
750-8207/025-001	PFC200 CS 2ETH RS 3G Tele T
750-8202/040-000	PFC200 CS 2ETH RS XTR
750-8202/040-001	PFC200 CS 2ETH RS Tele XTR
750-8206/040-000	PFC200 CS 2ETH RS CAN DPS XTR
750-8206/040-001	PFC200 CS 2ETH RS CAN DPS Tele XTR

31.1 System

[NEW]	WAT12376	Add localdomain.lan as default domain
[NEW]	WAT13150	Use the NTP server address from DHCP request answer
[NEW]	WAT13933	Target memory size is selectable if Create Boot Image is used
[NEW]	WAT13970	Change default assignment of the serial Interface to unassigned
[NEW]	WAT13980	Extend the service interface with Linux console
[NEW]		openVPN/ipsec configuration via web page of web based management
[NEW]		starting phases of the device are better signalled by LEDs, boot phase is represented by flashing SYS LED
[FIXED]	WAT9839	Create Boot Image does not work with SD Cards greater or equal than 16 GB with FAT formatting cards
[FIXED]	WAT11931	Error in flow control of the serial interface avoid the reconfiguration
[FIXED]	WAT14196	Updated SSH-Daemon dropbear to latest release version 2015-67.
[FIXED]	WAT14473	Switching terminal bus extension does not work
[FIXED]	WAT15752	Correction of the SYS-LED blink codes
[FIXED]	WAT15896	Security: to many internal or detailed information in error messages
[FIXED]	WAT16500	DHCP Settings override static parameter

[FIXED]	WAT16515	Missing data file synchronization by FTP put command
[FIXED]	WAT16854	Memory leaks in internal diagnostic system
[FIXED]	WAT17099	Failure of all LED on the controller in continuous operation at high CPU load off
[FIXED]	WAT17271	Auto mount of the SD Card does not work sometimes
[KNOWN]	WAT12485	FW05 downgrade to <= FW04 in flash returns an error message. A special image of the relevant firmware is needed to downgrade

31.2 Runtime System

[NEW]	WAT12486	e!RUNTIME: New CODESYS runtime version 3.5.6.0
[NEW]	WAT10429	Configuration file is stored in the same directory as the boot project – this allows the boot project as be copied via FTP
[NEW]	WAT10430	e!RUNTIME: Revised calculation of the load of the system
[NEW]	WAT12489	Revised behavior of RUN LED
[NEW]	WAT12490	Reset button functionality has been revised
[NEW]	WAT17034	e!RUNTIME: performance improvement in the webserver that is used for web visualization
[FIXED]	WAT11508 a.o.	Fixed various visualization errors to 3.5.6.0 (SP6, P0)
[FIXED]	WAT12077	Access to files caused latency in the RT tasks
[FIXED]	WAT12492	Directories “codesys” and “codesys3” merged to directory “runtime”
[FIXED]	WAT14603	e!RUNTIME: Storage of alarms in a file does not work
[FIXED]	WAT15408	CODESYS V2.3: Web-Visualization does not work with disabled CODESYS port.
[FIXED]	WAT15619	Task system with large time leads to long delays in project download
[FIXED]	WAT15781	KBus stops when logging on with an active port authentication
[FIXED]	WAT15787	Create boot application influences the task execution
[FIXED]	WAT16049	handling boot project location faulty when SD card is not plugged but configured
[FIXED]	WAT16062	Error message License expired in Web visu appears when boot project location on SD card
[FIXED]	WAT16234	e!RUNTIME: occasional crash during download of a project
[FIXED]	WAT16294	Incorrect privileges at USER and ADMIN for files that are generated by the RUNTIME
[FIXED]	WAT16317	Failure of all LED in continuous operation at very high CPU load
[FIXED]	WAT16431	e!RUNTIME: Task watchdog can lead to the disconnection to the device
[FIXED]	WAT16810	e!RUNTIME: runtime exception while debugging with breakpoints
[FIXED]	WAT17161	CODESYS V2.3: Multicast address for network variables does not work

- [KNOWN] WAT17595 e!RUNTIME: A string variable which is declared in the retain declaration part of a program forces an error while downloading if the string length is equal (i.e. 80).
Workaround: use a different odd length like 79.
- ```
PROGRAM POU
VAR RETAIN
 myString1: STRING; (* with error *)
 myString2: STRING(79); (* working *)
END_VAR
```
- All variables in structures must be declared with a 4-byte alignment and string variables in structures must use an odd length.
- [KNOWN] The Telecontrol functionality is only available together with CODESYS V2.3 on the devices.

### 31.3 Web Based Management

- [NEW] WAT10544 Built configuration pages for 3G modem
- [NEW] WAT12308 Added information field of related parameters via DHCP
- [NEW] WAT13981 Built configuration page for openVPN/IPsec
- [FIXED] WAT10763 Inserted a new field for the currently used PROFIBUS address
- [FIXED] WAT14048 Firewall configuration page is too slow

### 31.4 Operating System

- [NEW] WAT12513++ Use Linux Kernel 3.18.13 rt10
- [FIXED] WAT15348 During the download of certain projects, the K-Bus stops shortly
- [FIXED] WAT15407 In the recipe selection within the WebVisu, wtc files cannot be loaded or deleted

### 31.5 Fieldbus Interface & Protocols

#### Modbus

- [FIXED] WAT15738 Problems with FC66 data length. The length is limited to 700 registers
- [FIXED] WAT16769 RTU Slave: Error occurred during program download with active flow control
- [FIXED] WAT17187 CODESYS V2.3: Incorrect Modbus configuration (Stop bit == 1 and Parity == None) crashes the Runtime

#### CAN/CANopen

- [FIXED] WAT13692 Master does not start guarding with setting "No initialization"
- [FIXED] WAT14076 Master does not restart slave after guarding error
- [FIXED] WAT14359 No automatic restart at bus error  
WAT16298
- [FIXED] WAT14373 Master does not assume sync consuming parameters

|         |          |                                                                                          |
|---------|----------|------------------------------------------------------------------------------------------|
| [FIXED] | WAT14570 | CODESYS V2.3: PFC200 as CAN-Layer2 device can't receive telegrams after program download |
| [FIXED] | WAT15121 | Master treated slaves without static configuration in the IDE wrong                      |
| [FIXED] | WA15648  | The blink code of the CAN LED is incorrect when Guarding Error                           |

## Profibus

|    |      |
|----|------|
| [] | None |
|----|------|

### 31.6 Libraries

|         |          |                                                                                                                                       |
|---------|----------|---------------------------------------------------------------------------------------------------------------------------------------|
| [NEW]   | WAT10385 | e!RUNTIME: Implementation of the dynamic K-Bus configuration                                                                          |
| [NEW]   | WAT10539 | CODESYS V2.3: SMS transfer via IEC Library SMS_01.lib and e!RUNTIME: WagoAppSerial_Sms.lib supported                                  |
| [NEW]   | WAT12372 | e!RUNTIME: WagoAppSNMP.Lib.was added                                                                                                  |
| [NEW]   | WAT12373 | e!RUNTIME: WagoAppFTP.Lib was added                                                                                                   |
| [NEW]   | WAT13928 | Using the new toolchain for documentation creation of e!RUNTIME libraries leading to better content presentation                      |
| [NEW]   | WAT16393 | CODESYS V2.3: BusDiag.lib: New implementation of the error codes for Bus fault → PreOp and Stopped<br>Bus not communicating → Bus off |
| [FIXED] | WAT10772 | Compatible implementation of the interface RS232 at Online Change                                                                     |
| [FIXED] | WAT11484 | e!RUNTIME: WagoSysAtomic Interface compatible newly created                                                                           |
| [FIXED] | WAT11780 | CODESYS V2.3: WagoConfigTool.Lib function IP_TO_STRING provides false return value                                                    |
| [FIXED] | WAT13882 | CODESYS V2.3: Expansion of the WagoLibSSL.lib result of new TLS1.2                                                                    |
| [FIXED] | WAT14610 | Error process data access in WagoLibKBus.lib after online change                                                                      |
| [FIXED] | WAT14718 | Incorrect handling of parity errors in WagoSysCom.                                                                                    |
| [FIXED] | WAT14899 | CODESYS V2.3: Function SysDirRead treats the file pointer wrong                                                                       |
| [FIXED] | WAT15665 | Frame Error or Parity Error in the on board serial interface                                                                          |
| [FIXED] | WAT16103 | CODESYS V2.3: SNMP when sending a trap with version v2c via a host name the Runtime may crash                                         |
| [FIXED] | WAT16627 | CODESYS V2.3: WagoLibSSL.lib After online change a connection is not possible                                                         |
| [FIXED] | WAT16734 | CODESYS V2.3: Functions of the SyslibSocketsAsync.lib return error                                                                    |
| [FIXED] | WAT16746 | CODESYS V2.3: WagoLibLed.lib: Function LED_GET_STATE always provides the value 0 for the LED color                                    |
| [FIXED] | WAT17161 | CODESYS V2.3: SysSockSetOptions() supports no Multicast groups                                                                        |
| [KNOWN] | WAT18533 | Requesting the signal strength form the 750-8207 modem may hold the calling CODESYS task.                                             |

## 32 Firmware Release 02.04.21 (05)

Because of a serious error, the firmware has been blocked again.

### 32.1 Firmware Release 02.03.23 (04)

| Affected articles/Available for |                             |
|---------------------------------|-----------------------------|
| Article Number                  | Designation                 |
| 750-8202                        | PFC200 CS 2ETH RS           |
| 750-8203                        | PFC200 CS 2ETH CAN          |
| 750-8204                        | PFC200 CS 2ETH RS CAN       |
| 750-8206                        | PFC200 CS 2ETH RS CAN DPS   |
| 750-8202/025-000                | PFC200 CS 2ETH RS T         |
| 750-8203/025-000                | PFC200 CS 2ETH CAN T        |
| 750-8204/025-000                | PFC200 CS 2ETH RS CAN T     |
| 750-8206/025-000                | PFC200 CS 2ETH RS CAN DPS T |

### 32.2 System

|         |          |                                                                                                                                          |
|---------|----------|------------------------------------------------------------------------------------------------------------------------------------------|
| [NEW]   | WAT10540 | Firewall IP / Ports                                                                                                                      |
| [NEW]   | WAT9785  | Broadcast Protection / ICMP Protection                                                                                                   |
| [NEW]   | WAT10549 | Traffic Limitation, Port Mirroring                                                                                                       |
| [NEW]   | WAT10538 | MAC Address Filter                                                                                                                       |
| [NEW]   | WAT10462 | Local DHCP Server (not activated by default)                                                                                             |
| [NEW]   | WAT10462 | Local DNS Server (not activated by default)                                                                                              |
| [NEW]   | WAT10463 | NTP-Client supports up to 4 NTP-Servers                                                                                                  |
| [NEW]   | WAT      | Domain name und gateway are taken from the DHCP Request                                                                                  |
| [FIXED] | WAT9204  | CpuUsage: monitoring requires excessive CPU load                                                                                         |
| [FIXED] | WAT9972  | WAGO Ethernet-Settings / IO-Check: communication speed is low                                                                            |
| [FIXED] | WAT10504 | IO-Update: communication speed is low                                                                                                    |
| [FIXED] | WAT11377 | Security improvement: Port of WAGO tools can be deactivated by user                                                                      |
| [FIXED] | WAT11799 | Local bus with only end module leads to usage of 100% cpu load                                                                           |
| [FIXED] | WAT11912 | WAGO-Ethernet-Settings communication with controller temporary stops                                                                     |
| [FIXED] | WAT11939 | Factory Reset does not reset all parameters                                                                                              |
| [FIXED] | WAT12452 | Security improvement: bash code injection vulnerability (shellshock)                                                                     |
| [FIXED] | WAT12819 | Security improvement: OpenSSL update to 1.0.0o                                                                                           |
| [FIXED] | WAT13289 | WAGO-Ethernet-Settings: COM port is disabled after writing the settings.                                                                 |
| [FIXED] | WAT13291 | WAGO-Ethernet-Settings: IP settings are activated in sequence. This makes it possible that devices lose their connection to the network. |
| [FIXED] | WAT13839 | SNMP: Traps in SNMP V3 are transmitted twice.                                                                                            |
| [FIXED] | WAT13911 | IO-LED: When booting the error code "Recoverable Error" is blinking.                                                                     |
| [FIXED] | WAT14079 | Internal flash file system saves changes too late (data security in case of unforeseen shut down)                                        |
| [KNOWN] | WAT13366 | Ethernet-Settings: Cannot setup the second default gateway.                                                                              |

[KNOWN] WAT13838 Please use WAGO-Ethernet-Settings with at least version 06.03.01 (01).

### 32.3 Runtime System

[NEW] e!RUNTIME (CODESYS 3 based) runtime system released for the first time.

[NEW] CODESYS runtime can be selected or disabled

[FIXED] WAT11400 CODESYS V2.3: Bit access to same byte within different Tasks does not work

[FIXED] WAT11957 CODESYS V2.3: PLC configuration: Process data assigned to wrong addresses after 512 bytes

[FIXED] WAT12509 RS485 onboard interface receives character send by itself

[FIXED] WAT12564 Control Mode could be activated while PLC in run

[FIXED] WAT13195 Compiler Error with nested function calls

[FIXED] WAT12782 Control Mode does not work if eth port X1 is not connected

[FIXED] WAT12786 CODESYS V2.3: if PLC is started by PLC switch, task at breakpoint regardless runs

[FIXED] WAT13202 CODESYS V2.3: Cannot open COM port after CODESYS reset.

[FIXED] WAT14246 CODESYS V2.3: Cyclical, frequent call of function KBUS\_ERROR\_INFORMATION from WagoLibKbus.lib leads to task freeze.

[FIXED] WAT14851 The Webvisu Applet does not work if the boot project location is on memory card.  
INFO: Controller sets the USEURLCONNECTION = TRUE after project download internally.

[FIXED] WAT15378 Error in calculation in function REAL\_TO\_DWORD(-2);  
Expected result value is 4294967294(FFFFFFFFE),  
calculated result value is 4294967295(FFFFFFFFF).

[KNOWN] WAT10777  
WAT11008 CODESYS V2.3: project download with many persistent variables (> 10000) leads to communication timeout.  
Work-around: try to reconnect until success

[KNOWN] WAT15320 e!RUNTIME: Boot project will only be saved when the runtime is ready for RUN.

[KNOWN] WAT15348 e!RUNTIME: While project download modules can signal a bus error by LED on the module.

[KNOWN] WAT15407 e!RUNTIME: Error with WebVisu and recipe selection upon reading and deleting \*.wtc files.

[KNOWN] WAT15408 CODESYS V2.3: Webvisu does not work with deactivated CODESYS port. i.e. 2455.

[KNOWN] WAT13195 CODESYS V2.3: the use of CODESYS 2.3.9.47 is recommended in order to resolve compiler-related problems with CONCAT string functions and nested functions.

[KNOWN] CODESYS V2.3: various known issues in the 3S visualization.

## 32.4 Web Based Management

|         |                     |                                                              |
|---------|---------------------|--------------------------------------------------------------|
| [NEW]   | WAT10468            | Activate / deactivate the Runtime system CODESYS / e!RUNTIME |
| [FIXED] | WAT9629<br>WAT13208 | Password does not allow special characters                   |
| [FIXED] | WAT                 | Several security leaks                                       |
| [FIXED] | WAT9784             | Package Server does not work if system boot from SD card     |
| [FIXED] | WAT11386            | Security improvement: Login within WBM websites              |
| [FIXED] | WAT12000            | Security improvement: Command injection in WBM               |
| [FIXED] | WAT12200            | Page Diagnostics: list items not sorted by date              |
| [FIXED] | WAT12459            | Diagnostic: time stamp ignores time zone settings            |
| [FIXED] | WAT12748            | Page areas were shown twice occasionally                     |
| [FIXED] | WAT14121            | Cannot remove all DNS Servers from list. Last item remains.  |
| [KNOWN] | WAT14073            | SNMP: Authentication Key is displayed in WBM in plain text.  |

## 32.5 Operating System

|         |          |                                             |
|---------|----------|---------------------------------------------|
| [NEW]   | WAT10436 | File system NTFS supported on SD card       |
| [FIXED] | WAT11907 | Multicast packet transmission does not work |

## 32.6 Fieldbus Interface & Protocols

### Modbus

|         |          |                                                                                                                 |
|---------|----------|-----------------------------------------------------------------------------------------------------------------|
| [FIXED] | WAT12785 | RTU: PLC access interface is not locked with Linux Console                                                      |
| [FIXED] | WAT15459 | RTU: Upon receipt of erroneous frames the Modbus slave takes a long time until it synchronizes again on frames. |

### CAN/CANopen

|         |          |                                                                                |
|---------|----------|--------------------------------------------------------------------------------|
| [NEW]   | WAT10982 | CODESYS V2.3: CAN Layer2 as device in dialog "PLC configuration"               |
| [FIXED] | WAT9475  | CANopen Slave Sync monitoring does not work with Object 0x1006                 |
| [FIXED] | WAT      | WagoCANopen_02.lib – several bugs                                              |
| [FIXED] | WAT12770 | WagoCANLayer2_01.lib – several bugs                                            |
| [FIXED] | WAT9535  | BusDiag.lib – STATE variable delivers wrong values                             |
| [FIXED] | WAT9556  | CANopen Master starts the slaves not reliable                                  |
| [FIXED] | WAT11359 | Memory leak while project download                                             |
| [FIXED] | WAT12120 | PFC200 sends message START_ALL_NODES instead of START_NODE to projected slaves |
| [FIXED] | WAT12744 | CANopen Master start of slaves after short BusOff not reliable                 |
| [FIXED] | WAT14128 | CAN Bus Startup is unstable with many slaves.                                  |
| [FIXED] | WAT14161 | In case of short-term bus errors, the slave startup again unreliable.          |

## Profibus

- [FIXED] WAT12975 GSD settings use wrong byte order (Motorola/Intel)
- [FIXED] WAT14148 Modul parameter uses wrong byte orientation (motorola/intel format) in gsd file for third party plcs (Siemens S7).

### 32.7 Libraries

- [NEW] WAT10837 CODESYS V2.3: WagoLibNetSnmpManager.lib with support of Traps, Notification and Inform.
- [FIXED] WAT Kbus Lib
- [FIXED] WAT9332 SerComm.lib: support new feature in 750-652 (SW04, DMX data transfer)
- [FIXED] WAT9992 SerComm.lib: communication via onboard interface cannot transmit data if more than 512 bytes should send
- [FIXED] WAT11765 SysLibFile.lib: Function SysFileDelete does not release file handles
- [FIXED] WAT12128 IEC61850: Goose communication as publisher not possible
- [FIXED] WAT12157 WagoLibKbus.lib: crash after multiple registration of data
- [FIXED] WAT13353 CODESYS V2.3: Wrong digital offset calculation in system libraries mod-com.lib and WagoLibKBus.lib.
- [FIXED] WAT13993 CODESYS V2.3: WagoLibNetSnmpManager.lib SNMP\_NULL\_TO\_TLV can not be used.
- [FIXED] WAT13999 CODESYS V2.3: Serial\_Interface\_01.lib FB\_Serial\_Interface does not work after online change.
- [FIXED] WAT14085 CODESYS V2.3 Sercomm.lib: wrong configuration handling of unconfigurable serial module (750-653)
- [FIXED] WAT14728 WAT14729 CODESYS V2.3 BusDiag.lib: DiagGetBusState does not return an error if DEVICENUMBER is invalid.
- [FIXED] WAT14731 CODESYS V2.3 BusDiag.lib: DiagGetState does not return an error if BUSMEMBERID is invalid.
- [FIXED] WAT15418 CODESYS V2.3 modb\_I05.lib with Modbus RS485: After program download, the interface cannot be opened sporadically.

## 33 Firmware Release 02.02.20 (03)

| Affected articles/Available for |                           |
|---------------------------------|---------------------------|
| Article Number                  | Designation               |
| 750-8202                        | PFC200 CS 2ETH RS         |
| 750-8203                        | PFC200 CS 2ETH CAN        |
| 750-8204                        | PFC200 CS 2ETH RS CAN     |
| 750-8206                        | PFC200 CS 2ETH RS CAN DPS |

|                  |                                 |
|------------------|---------------------------------|
| 750-8202/025-000 | PFC200 CS 2ETH RS T             |
| 750-8203/025-000 | PFC200 CS 2ETH CAN T            |
| 750-8204/025-000 | PFC200 CS 2ETH RS CAN T         |
| 750-8206/025-000 | PFC200 CS 2ETH RS CAN DPS T     |
| 750-8202/025-001 | PFC200 CS 2ETH RS TELE T        |
| 750-8202/025-002 | PFC200 CS 2ETH RS ECO TELE T    |
| 750-8206/025-001 | PFC200 CS 2ETH RS CAN DPS TELET |

### 33.1 System

- [NEW]      WAT10466      SSL3.0 and TLS1.1 is provided (RFC6101, RFC5246) (openssl) for use in other library services
- [NEW]      WAT10465      SNMP extension in WagoLibNetSnmpManager library.
- [NEW]      WAT10461      Dual-LAN is configurable / activated by WBM
- [NEW]      WAT9679        LED signals an error even though CANopen is not configured/used.

### 33.2 Runtime System

- [NEW]      WAT11632      New TargetIDs for all PFC200 controllers  
Projects must be recompiled, so an erroneous instruction sequence can be found.
- [FIXED]    WAT12586      Incorrect data on the K-Bus at breakpoint / single-step / debugging
- [FIXED]    WAT12224      Error in downloading projects with big visuals
- [FIXED]    WAT10147      Download as file blocked K-Bus

### 33.3 Web Based Management

- [NEW]                      Performance improvement on reaction time
- [NEW]                      HTTPS for web visualisation

### 33.4 Operating System

- [NEW]                      Kernel features for IPsec, VPN, OpenVPN activated
- [FIXED]    WAT11874      LED-server crashes sporadically
- [FIXED]    WAT11945      SYS-LED turns red after several resets (Overload detection is incorrect)

### 33.5 Fieldbus Interface & Protocols

- [NEW]                      Modbus configurable response delay
- [FIXED]    WAT11378      TCP Keep-Alive
- [FIXED]    WAT12779      DALI Configurator (753-647 DALI Multi-Master-clamp) and I/O-check work at 4 times the speed communication.  
WAT12644
- [FIXED]    WAT11703      Access error with simultaneous Word and Bit access of adjoining K-Bus variables.



- [FIXED]    WAT9944    Modbus RTU Slave reimplementation of the RTU parser caused by lost data bytes.
- [FIXED]    various WAT    fixed various CANopen errors

### 33.6 Libraries

- [NEW]                      WagoLibKBus.lib  
This library supports the reading and writing of data points in synchronism with the task K-Bus
- [NEW]                      WagoCANLayer2\_02.lib  
This library supports the reading and writing of data on Layer 2 level
- [FIXED]    WAT9677    WagoCANopen\_02.lib changes the behavior to meet the documentation
- [FIXED]    WAT10106    SysLibCom: SysComWrite does not send all data on the line

## 34 Firmware Release 02.01.10 (02)

| Affected articles/Available for |                              |
|---------------------------------|------------------------------|
| Article Number                  | Designation                  |
| 750-8202                        | PFC200 CS 2ETH RS            |
| 750-8203                        | PFC200 CS 2ETH CAN           |
| 750-8204                        | PFC200 CS 2ETH RS CAN        |
| 750-8206                        | PFC200 CS 2ETH RS CAN DPS    |
| 750-8202/025-001                | PFC200 CS 2ETH RS TELE T     |
| 750-8202/025-002                | PFC200 CS 2ETH RS ECO TELE T |

### 34.1 System

No updates

### 34.2 Runtime System

No updates

### 34.3 Web Based Management

No updates

### 34.4 Operating System

No updates

### 34.5 Fieldbus Interface & Protocols

- [NEW]                      changes to pass comdec test

## 34.6 Libraries

No updates

## 35 Firmware Release 02.01.04 (01)

| Affected articles/Available for |                           |
|---------------------------------|---------------------------|
| Article Number                  | Designation               |
| 750-8202                        | PFC200 CS 2ETH RS         |
| 750-8203                        | PFC200 CS 2ETH CAN        |
| 750-8204                        | PFC200 CS 2ETH RS CAN     |
| 750-8206                        | PFC200 CS 2ETH RS CAN DPS |

## 35.1 System

[NEW]

Firmware released first time  
CODESYS Version: 2.4.7.x  
LINUX Version: 3.6.11